

K 7777 B

Built-in refrigerator, 178 cm niche height

FlexiLight 2.0, PerfectFresh Active – active humidification for best freshness.



- Fresh 5x longer with active humidification – PerfectFresh Active
- Individually adjustable glass shelf lighting with FlexiLight 2.0
- Uniform temperature distribution inside the appliance – DynaCool
- Door shelf heights can be adjusted individually
- No visible condensation thanks to dry CleanSteel back wall



EAN: 4002516895336 / Material number: 12819500 /
Old Material Number: 36777702EU1

General information	
Model identifier	K 7777 B
Manufacturer material number	12819500
EAN number	4002516895336
Marketing class	Platinum
Appliance category	
Refrigerator	•
Construction type	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Convertible door hinging	•
Design	
Refrigeration section lighting	FlexiLight 2.0
Fan lighting	•
Freshness system lighting	•
User convenience	
Networking with Miele@home	•
Freshness system	PerfectFresh Active
Fine adjustment inner door	•
ComfortClean	•
ComfortSize	•
DynaCool	•
Party mode	•
Holiday mode	•
SoftClose	•
SelfClose	•
Ice/Water dispenser with mains water connection	No
Control system	
Operating concept	FreshTouch
Fridge compartment can be switched off	Yes
SuperCool	•
No. of temperature zones	2
Sabbath mode	•
Fridge/Fridge section	
No. of shelves	7
including number of split shelves (FlexiBoard)	1
of which illuminated	4
Chrome-plated metal bottle rack	•
No. of crisper drawers	3
Dry back wall	CleanSteel
Number of inner door racks for tinned food	3
Door rack for bottles	2
Door shelves	5
Efficiency	
Energy efficiency class (A–G)	B
Annual energy consumption in kWh	79.57
Energy consumption in 24 h in kWh	0.21

K 7777 B

Built-in refrigerator, 178 cm niche height

FlexiLight 2.0, PerfectFresh Active – active humidification for best freshness.




EAN: 4002516895336 / Material number: 12819500 /
Old Material Number: 36777702EU1

Safety	
Lock function	•
Acoustic door alarm	•
Optical door alarm	•
Technical data	
Niche width in mm min.	560
Niche width in mm max.	570
Niche height in mm min.	1772
Niche height in mm max.	1788
Niche depth in mm	550
Appliance dimensions (W x H x D) in mm	559 x 1770 x 546
Appliance width in mm	559
Appliance height in mm	1770
Appliance depth in mm	546
Weight in kg	72.7
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	26
Climate range	SN-T
Refrigerator compartment in l	296
including PerfectFresh zone in l	98
Of which pantry compartment in l	296
Total usable capacity in l	296
Acoustic airborne noise emission class (A–D)	A
Sound emissions in dB(A) re 1 pW	29
Current consumption (mA)	1200
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50-60
Length of supply lead in m	2.2
Replacing lamps	Service
Accessories included	
Egg tray	•
PerfectFresh organisation box	•

K 7777 B


Built-in refrigerator, 178 cm niche height

FlexiLight 2.0, PerfectFresh Active – active humidification for best freshness.




K7733E, K7763E, K7732E, K7734F, K7764E, K7743E, K7744E, K7773D, K7774D

1. View from the front, 2. Mains connection cable, L = 2200 mm, 3. Ventilation cut-out min. 200 cm², 4. Ventilation, 5. No connections permitted in this area



K7733E, K7763E, K7732D, K7732E, K7734F, K7764E, K7743E, K7744E, K7773D, K7774D, built-in

*The declared energy consumption was calculated in a 560 mm deep niche. The appliance is fully functional in a 550 mm niche but the energy consumption will be slightly higher.



K7733E, K7763E, K7732E, K7734F, K7764E, K7743E, K7744E, K7773D, K7774D, side view