

G 5811 SC Front Active Plus Freestanding dishwashers for optimum drying results thanks to AutoOpen drying.



- Best energy efficiency class A – energy-saving and eco-friendly
- Perfect results in less than one hour – QuickPowerWash
- Innovative design and maximum convenience – 3D MultiFlex Tray
- Fresh water dishwashers – from 6.0 l litres in the Automatic programme
- Save up to 50 % more electricity – hot water connection
- Versatile and secure – comfort basket design



EAN: 4002516913689 / Material number: 12864970 / Old Material Number: 21581118GB

Model	
Freestanding dishwasher	•
60 cm dishwasher	•
Design	
Control panel colour	CleanSteel front
Control panel version	Straight fascia
Control type	Programme selector button
Display	3-digit 7-segment display
Display colour	White
Convenience	
Door closing aid	AutoClose
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	Display
Efficiency and sustainability	
Energy efficiency class (A–G)	A
Water consumption in the Automatic programme in l from	6.0
Water consumption of the ECO programme in litres per programme cycle	8.2
Electricity consumption in the ECO programme in kWh	0.54
Energy consumption of the ECO programme in kWh after 100 programme cycles	54
Consumption value in kWh in the ECO programme with hot water connection	0.30
Duration of ECO programme in minutes	258
Number of place settings	14
Noise emission class	B
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
AutoOpen drying	•
BrilliantGlassCare	•
Wash programmes	
QuickPowerWash	•
ECO	•
Automatic	•
Intensive 75 °C	•
Gentle	•
Dishwashing options	
Express	•
Extra Clean	•
Extra dry	•
Basket design	
Cutlery loading	3D MultiFlex tray
FlexCare cup rack	1
Basket design	Comfort

G 5811 SC Front Active Plus
Freestanding dishwashers
for optimum drying results thanks to AutoOpen drying.



EAN: 4002516913689 / Material number: 12864970 / Old Material Number: 21581118GB

Safety

Waterproof system

•

Safety lock

•

Technical data

Niche width minimal in mm

600

Niche width max in mm

600

Niche height minimal in mm

845

Niche height maximal in mm

880

Niche depth in mm

600

Appliance width in mm

598

Appliance height in mm

845

Appliance depth in mm

600

Depth with door open in cm

119.5

Net weight in kg

54.5

Total rated load in kW

2.00

Voltage in V

230

Fuse rating in A

10

Number of phases

1

Electrical frequency standard

50

Length of water inlet hose in cm

1.50

Length of water drain hose in cm

1.50

Length of supply lead in m


1.80

Accessories included

Voucher for 1 x box of UltraTabs (20 tabs) or 3 boxes (60 tabs in each) at a reduced price

•

G 5811 SC Front Active Plus
Freestanding dishwashers
for optimum drying results thanks to AutoOpen drying.



G7000, free standing dishwasher, 60cm (installation drawing)