

## Triflex HX3 Plus

Cordless stick vacuum cleaners

high suction power | up to 140 min running time | flooring detection | HEPA



- Dust pickup >99.99 %\* for thorough and hygienic deep cleaning
- Boost mode: for faster cleaning of heavily soiled areas
- Running time: up to 140 minutes\*\*\* with VARTA lithium-ion rechargeable battery.
- Patented\*\*\* 3-in-1 design incl. self-standing feature for parking
- HEPA filter: 99.999 %\*\*\*\* exhaust air filtration for the purest ambient air
- FloorDetect: automatic flooring detection and power adjustment
- BrilliantLight: particularly bright LED front light for maximum dust detection
- Display: shows time left and important data for stress-free vacuuming
- Twist2open: for hygienic and easy emptying of the dust container
- Carefully developed and manufactured in Germany by Miele & Cie. KG
- Premium set: including Hardfloor Care Tool and second battery

\* When picking up dust on hard floors with cracks, we achieve > 100 % dust pickup in power level HI, measured according to IEC 62885-4:2024

\*\* Valid for power level MIN without connected Multi Floor XXL electrobrush and when using 2 rechargeable batteries

\*\*\* Patent: DE 10 2016 105 475 B4

\*\*\*\* 99.999 % according to IEC 62885-4:2020/HEPA according to EN 1822-1:2019

EAN: 4002516922506 / Material number: 12878430 / Old Material Number: 41WDL034GB

<b>General information</b>	
Model identifier	Triflex HX3 Plus
Manufacturer material number	12878430
EAN number	4002516922506
<b>Construction type</b>	
Cordless stick vacuum cleaners	•
Product brand	Triflex HX3
Motor type	Digital Efficiency Motor
Product type	SWDLO
<b>Appliance type and design</b>	
Appliance colour	Titanium PF
<b>Cleaning</b>	
Vortex Technology	•
MultiFloor XXL SEB 435 electrobrush with BrilliantLight	•
<b>User convenience</b>	
Park system for pauses during vacuuming	•
Exchangeable Li-Ion battery	•
3-in-1 design	•
<b>Filter system</b>	
ComfortClean	•
Exhaust filter	HEPA lifetime filter
Dustbag volume in l	0.5
<b>Technical data</b>	
Battery type	Li-ion
Nominal battery capacity in mAh	2500
Volume in dB	74.0
Width in mm	260
Height in mm	1297
Depth in mm	280
Weight in kg	3.6
Volt	25,2
High level running time PowerUnit solo	2 x 70
LOW level running time with electrical accessories	2 x 38
High level running time with electrical accessories	2 x 15
Cleaning area in m <sup>2</sup>	2 x 160
Recharging time in min.	240
<b>Accessories included</b>	
HX-DB dusting brush	•
XL HX-UN upholstery nozzle	•
HX-CN crevice nozzle	•
HX-AH accessories holder	•
MultiFloor XXL electrobrush with BrilliantLight	•
Cleaning tool	No
Wall Mount	•
Power supply unit	•
Additional battery	•
Hardfloor Care soft roller	•