


KM 8685-2 FL MattFinish
 Induction hob with onset controls
 800 mm | Full-surface | M Sense ready | MattFinish



- Resistant matt surface for a sophisticated kitchen design – MattFinish
- Full-surface induction for up to 6 items of cookware
- Precise settings via 6 MultiSlide sliders including intelligent networking
- Prepared for cooking and frying assistance with M Sense cookware – M Sense ready
- A width of 800 mm for surface-mounted or flush-fit installation
- Shortest heat-up times thanks to Booster level

EAN: 4002516975991 / Material number: 12948320 /
 Old Material Number: 26186855GB

| General information | |
|--|-------------------------|
| Model identifier | KM 8685-2 FL MattFinish |
| Manufacturer material number | 12948320 |
| EAN number | 4002516975991 |
| Marketing class | Platinum |
| Heating type | |
| Heating type | Induction |
| Construction type | |
| Independent of cooker | • |
| Design | |
| Elegant glass ceramic surface | • |
| Ceramic surface colour | Matt black |
| Scratch-resistant surface | MattFinish |
| Flush | • |
| Surface-mounted installation | • |
| Cooking zone details | |
| Number of cooking zones | 1 |
| Number of cooking areas | 1 |
| Maximum number of pans | 6 |
| 1st cooking zone/cooking area | |
| Position | Can be selected freely |
| Type | Full area |
| Size in mm | 740x380 |
| Max. rating in W | 2600 |
| Max. Booster power rating in W | 3650 |
| User convenience | |
| Networking with Miele@home | • |
| Con@ctivity | • |
| Pan and pan size recognition | • |
| M Sense ready | • |
| Operation via sensor controls | MultiSlide |
| Display colour | White |
| Intelligent pan recognition | • |
| Professional mode | • |
| Stop & Go function | • |
| Wipe protection | • |
| Recall function | • |
| Minute minder | • |
| Safety switch-off | • |
| Auto heat-up | • |
| Keeping warm | • |
| Individual setting options (e.g. buzzers) | • |
| Assistance programmes | • |
| Efficiency and sustainability | |
| Power rating in off mode in W | 0.3 |
| Power rating in standby mode in W | 0.8 |
| Power rating in networked standby in W | 2.0 |
| Time until automatic switch to off mode in min | 10 |

KM 8685-2 FL MattFinish
 Induction hob with onset controls
 800 mm | Full-surface | M Sense ready | MattFinish



EAN: 4002516975991 / Material number: 12948320 /
 Old Material Number: 26186855GB

| | |
|--|-------------------|
| Time until automatic switch to standby in min | 10 |
| Time until automatic switch to networked standby in min | 10 |
| Cleaning and care | |
| Easy to clean ceramic glass | • |
| Safety | |
| Safety switch-off | • |
| Lock function | • |
| System lock | • |
| Integrated cooling fan | • |
| Overheating protection | • |
| Residual heat indicator | • |
| Technical data | |
| Dimensions (H x W x D) in mm | 51 x 800 x 52 |
| Dimensions (W x D) in mm | 800 x 51 x 52 |
| Dimensions in mm (width) | 800 |
| Dimensions in mm (height) | 51 |
| Dimensions in mm (depth) | 52 |
| Cut-out dimensions (W x D) with surface-mounted installation in mm | 780 mm x 500 mm |
| Cut-out dimensions (W x D) with flush-fit installation in mm | 780/804 x 500/524 |
| Casing height incl. connection box in mm | 51 |
| Cutout dimensions in mm (width) with surface-mounted installation | 780 mm |
| Cutout dimensions in mm (depth) with surface-mounted installation | 500 mm |
| Internal cutout dimensions in mm (width) with flush installation | 780 |
| Internal cutout dimensions in mm (depth) with flush installation | 500 |
| Weight in kg | 19 |
| External cutout dimensions in mm (width) with flush installation | 804 |
| External cutout dimensions in mm (depth) with flush installation | 524 |
| Total rated load in kW | 9.20 |
| Length of supply lead in m | 1.6 |
| Voltage in V | 230 |
| Frequency in Hz | 50-60 |
| Accessories included | |
| Mains cable | Yes |

