

TEL785WP Steam&9kg T1 heat-pump dryer:



EAN: 4002517000128 / Material number: 13018810 / Old Material Number: 12EL7852IRL

General information

Model identifier	TEL785WP Steam&9kg
Manufacturer material number	13018810
EAN number	4002517000128
Marketing class	Platinum

Construction type

Suitable for stacking	•
Door hinging	left
Side-by-side	•
Slot-in	•
Can be built-under	•

Model

Product brand	T1 Chrome Edition
Heat pump dryer	•

Design

Appliance colour	Lotus white
Control panel colour	Lotus white
Rotary selector colour	Lotus White / Chrome ring
Control panel version	Straight
Control type	Rotary control
Display	ComfortSensor white, 1 line

Drying results

PerfectDry precision drying	•
FragranceDos ² fragrance system	•
Intelligent drum reversal	•
HygieneDry	•

Gentle laundry care

SilenceDrum	•
Load in kg	9

User convenience

Networking with Miele@home	•
Wash2Dry	•
Delay start up to 24 hours	•
Time left display	•
Programme sequence indicator	No
Drum lighting	LED
MultiLingua	•
Acoustics package for the lowest sound emissions	•
Condensate container	•
Integrated condensed water drainage	•
AddLoad	•

Smart Extras

Consumption Dashboard	•
Wash2Dry	•
Push notifications	•
MobileStart	•
Alexa voice control	•
Google voice control	•

TEL785WP Steam&9kg T1 heat-pump dryer:



EAN: 4002517000128 / Material number: 13018810 / Old Material Number: 12EL7852IRL

AI Diagnostics	•
RemoteUpdate	•
Smart Home Integration	•
Efficiency	
Consumption estimate	•
DryProtect	•
Maintenance-free heat exchanger	•
DuraLife motor	•
Efficiency	
Energy efficiency class (A–G)	C
Condensation efficiency class (A–D)	A
Condensation efficiency in %	94
Weighted energy consumption per 100 cycles in the “ECO Normal” programme in kWh	101
Acoustic airborne noise emissions in the “ECO Normal” standard programme in dB(A) re 1 pW	62
Acoustic airborne noise emission class (A–D)	B
Programme running time in the “ECO Normal” programme in min	184
Drying programmes	
Automatic plus	•
Cottons (coloureds)	•
Cottons arrow	•
Minimum iron	•
Delicates	•
Shirts	•
Silks handcare	•
Woolens handcare	•
Express	•
Denim	•
Outerwear	•
Proofing	•
Sportswear	•
Standard pillows	•
Cool air	•
Warm air	•
Basket programme	•
Pre-Ironing	•
Bed linen	•
Steam care	•
Drying extras	
Anti-crease	•
Buzzer	•
DryCare 40	•
DryFresh	•
PowerFresh	•
Quality	
Soft ribs	•

TEL785WP Steam&9kg T1 heat-pump dryer:



EAN: 4002517000128 / Material number: 13018810 / Old Material Number: 12EL78521RL

Safety

PIN-Code	•
Empty out container indicator	•
Clean filter indication	•
Optical interface	•

Technical data

Dimensions (H x W x D) in mm	850 x 596 x 636
Dimensions in mm (width)	596
Dimensions in mm (height)	850
Dimensions in mm (depth)	636
Weight in kg	56
Voltage in V	220-240
Fuse rating in A	10
Frequency in Hz	50
Total rated load in kW	1.10
Length of supply lead in m	2.0
Hermetically sealed	•
Type of coolant	R290
Refrigerant quantity in kg	0.14
Refrigerant global warming potential in CO ₂ e	3
Appliance global warming potential in CO ₂ e	0.42
Replacing lamps	Service

Accessories included


Fragrance flacon	•
Voucher for a second fragrance flacon	•

Available display languages


Available display languages via MultiLingua

☐☐, ☐☐☐☐, deutsch, dansk, english (AU), english (GB), english (US), suomi, français (CA), français (FR), ελληνικά, italiano, ☐☐☐, ☐☐☐, hrvatski, bahasa malaysia, nederlands, norsk, polski, português, română, русский, svenska, srpski, slovenčina, slovenščina, español, čeština, türkçe, українська, magyar


TEL785WP Steam&9kg T1 heat-pump dryer:




T1 installation drawing, slanted facia or straight facia, measures in mm



T1 drawing, slanted facia or straight facia, measures in mm



T1 drawing, slanted facia or straight facia, with porthole, measures in mm



T1 drawing, slanted facia or straight facia, measures in mm