

PWD 8692 [DC5]

Thermal disinfectant and washer-disinfectant
with liquid dispensing & hot air drying DryPlus.



- Perf./cycle, e.g. 44 transmission instruments or 44 suction devices
- Throughput/cycle e.g. 8 DIN mesh trays or 48 GYN specula
- Safety through monitoring – wash pressure and spray arm monitoring
- Maximum user convenience with M Touch Flex full-touch colour display
- Efficient hot air drying – DryPlus
- Connectivity as standard via WiFi

EAN: 4002516999409 / Material number: 13053470 /
Old Material Number: 62869210NWE

Construction type and version

Construction type	Freestanding, can be built-under, slimline
Range	ExpertLine
Control panel colour	Black
Casing	White
Can be built-under	•
Lid	Stainless steel, lotus white coated
Number of wash levels	2
AutoClose – automatic door lock	•
Buzzer, acoustic signal at end of programme	•
Service-friendly design	•

Application

Suitable for hospitals	•
Suitable for dental surgeries	•
Suitable for doctors' surgeries	•
Suitable for outpatient surgeries	•
Suitable for veterinary practices	•
Suitable for podiatry practices	•

Capacity

DIN mesh trays per cycle [number]	8
MIS sets per cycle [number]	1-2
Ophthalmology sets per cycle [number]	8
GYN specula [number]	48
AN sets per cycle [number]	2-3
Theatre shoes per cycle [number]	28
Surgical saliva extractors per cycle [number]	44
Lumened instruments per cycle [number]	44
Transmission instruments per cycle [number]	44

Performance data

Circulation pump, Qmax in l/min	500
Wash cabinet usable capacity in l	145.00
Tested operating hours	15000
Maximum final rinse temperature in °C	93

Miele MOVE

Miele MOVE Connect (option)	•
Miele MOVE MedDent+ (option)	•

Control system

Control type	M Touch Flex
Process approval directly via the display	•
Max. delay start in h	24
Programmability	programmable
Programmes [number]	24
Free programme positions [number]	5
AO value controls	•
Time left display	•
Programme sequence display	•

PWD 8692 [DC5]

Thermal disinfectant and washer-disinfectant
with liquid dispensing & hot air drying DryPlus.



EAN: 4002516999409 / Material number: 13053470 /

Old Material Number: 62869210NWE

Selectable display languages

•

Standard electrical connection

Electrical connection	AC 230V 50HZ
Electric heater rating in kW	5.50
Total rated load in kW	6.30
Fuse rating in A	32
Length of mains connection cable in m	1.90

Possible voltage variant 1

Electrical connection	2 AC 230V 50HZ
Electric heater rating in kW	2.50
Total rated load in kW	3.30
Fuse rating in A	16

Water connection/drainage

Cold water [number]	1
Hot water [number]	1
Required flow pressure in kPa	200-1000
DI water [number]	1
Maximum delivery head for drain pump in cm	100
Maximum water hardness (cold water/hot water) in mmol/l	10.70
VEP feed pump for demineralised water (option)	•
Drain pump [DN]	22
Integrated water softener	•
Water protection system	Waterproof system

Drying unit

Integrated drying unit	•
Fan in kW	0.30
Heater element in kW	2.20
Air throughput in m³/h	60
Time setting in 1-minute increments	0-120
HEPA filter class	H13
HEPA filter filtration efficiency (in accordance with DIN EN 1822) in %	99.95
HEPA filter service life in h	200

Dimensions and weight

External dimensions, net height in mm	835
External dimensions, net width in mm	598
External dimensions, net depth in mm	598
External dimensions, gross height in mm	920
External dimensions, gross width in mm	670
External dimensions, gross depth in mm	740
Wash cabinet, usable height in mm	520
Wash cabinet, usable width in mm	530
Wash cabinet, depth of upper basket in mm	523
Net weight in kg	81
Wash cabinet, depth of lower basket in mm	520
Gross weight in kg	90
Maximum floor load in N/m²	1220

Emissions data

Emission sound pressure level in the workplace	≤70 dB(A) re 20 µPa
--	---------------------

PWD 8692 [DC5]

Thermal disinfectant and washer-disinfectant
with liquid dispensing & hot air drying DryPlus.

EAN: 4002516999409 / Material number: 13053470 /

Old Material Number: 62869210NWE

Heat dissipation into the room in MJ/h 3.96

Programmes	
Vario TD Intensive	•
Vario TD Dental	•
Vario Dental +	•
Vario TD Instr 4 mesh trays	•
Vario TD Instr 6 mesh trays	•
Vario TD Instr 8 mesh trays	•
Vario TD Container	•
Vario TD AN	•
Vario TD MIS	•
Vario TD GYN	•
Vario TD ENT	•
Vario TD ENT +	•
Vario TD ENT Optics	•
Ophthalmology	•
Ophtha tray A 207	•
Baby bottles	•
Theatre shoes	•
Ward utensils	•
Universal	•
Cold water rinse	•
Features	
1 door dispenser for rinse aid	•
1 dispenser pump for liquid cleaning agent	•
Volume flow control	•
Interface for process documentation (optional)	•
Suction lance for media canisters 10–20 l (optional)	•
Convenient suction lance DC5	•
Customer Service interface	•
Steam condenser	•
Spray pressure monitoring	•
Extensive components (option)	•
Spray arm monitoring	•
How-to sequences	•
Wash cabinet lighting	•
Multi-component filter system	•
Variable-speed heater pump	•
Load carrier – direct coupling	•
DryPlus	•
In-door salt container	•
Wash cabinet seamlessly welded using laser technology	•
Heater elements outside wash cabinet	•
Wash cabinet made from high-quality stainless steel (1.4301/304)	•
Connection options	
WiFi	•
Ethernet interface (optional)	•
External dispensing modules	•

PWD 8692 [DC5]
Thermal disinfectant and washer-disinfectant
with liquid dispensing & hot air drying DryPlus.



EAN: 4002516999409 / Material number: 13053470 /
Old Material Number: 62869210NWE

Standards, test certificates and symbols	
VDE (electrical safety)	•
IP safety class according to EN 60529: IP 21	•
EN 61010-2-040	•
EN 61010-1	•
RoHS guideline 2011/65/EU	•
EU medical device class IIb	•