


E 205

Insert

For the optimum loading of glasses.



- Suitable for lower basket U 890
- For 17 glasses with a diameter of 2.6 inches
- With perforated tray inlay to interrupt the water jet
- Rail height 8 3/4 (220) in (mm)
- The maximum vertical clearance with glasses is 10 3/4 (270) in (mm)


EAN: 4002511808874 / Material number: 03808980 / Old Material Number: 67520501D

Product category	
Fresh-water dishwashers	•
Machine affiliation	
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
Product category	
Insert for glasses	•
Product characteristics	
Material	Wire, rilsan-coated
Color	White
Number of rows	2
Rail height in mm	8 3/4 (220)
Maximum vertical clearance in mm	10 3/4 (270)
For use in lower basket	APFD 220, U 890
Capacity	
Glasses up to max. Ø 2 5/8" (66 mm) [number]	17
Standard electrical connection	
Number of phases	0
Voltage in V	0

E 205

Insert

For the optimum loading of glasses.



EAN: 4002511808874 / Material number: 03808980 / Old Material Number: 67520501D

Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in inches	221
External dimensions, net width in inches	243
External dimensions, net depth in inches	494
External dimensions, gross height in inches	9 1/8 (230)
External dimensions, gross width in inches	20 (505)
External dimensions, gross depth in inches	9 7/8 (250)
Net weight in lbs	4 (1.40)
Gross weight in lbs	4 (1.80)