

E 380
Mobile unit
for the optimum loading of narrow-neck glassware.



- equipped with 32 nozzles and locking mechanisms
- Equipped with connection for hot air drying
- Bracket for ML/2 for automatic mobile unit recognition

EAN: 4002511116467 / Material number: 03809880 / Old Material Number: 69538001D

Product category	
Washer-disinfectors, laboratory	•
Machine affiliation	
PG 8535	•
PG 8536	•
Product category	
Mobile unit with connection for hot-air drying	•
Mobile unit for narrow-neck glassware	•
Product characteristics	
Material	Stainless steel, Plastic
Color	Stainless Steel, Black
Application area	
Reprocessing of laboratory glassware	•
Capacity	
Narrow-neck glassware [number]	32
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in inches	19 13/16 (502)
External dimensions, net width in inches	21 1/8 (535)
External dimensions, net depth in inches	20 3/8 (517)
External dimensions, gross height in inches	21 1/2 (545)
External dimensions, gross width in inches	6 5/16 (160)
External dimensions, gross depth in inches	20 7/8 (530)
Net weight in lbs	18 (7.90)
Gross weight in lbs	19 (8.60)
Accessory pack	
E 351 injector nozzle, Ø 3/16" (4 mm), length 6 5/16" (160 mm) [number]	14
E 352 injector nozzle, Ø 1/4" (6 mm), length 8 11/16" (220 mm) [number]	18
E 353 clip for injector nozzle E 351 [number]	14
E 354 clip for injector nozzle E 352 [number]	18
Rinse nozzle for powder dispenser [number]	1