

E 313

Wall fitting

for the manual production of demineralized water.



- Pressurized to 10 bar
- Complete with pressure hose 150 cm

EAN: 4002511115279 / Material number: 03830330 / Old Material Number: 69431301D

Product category	
Fresh-water dishwashers	•
Tank dishwashers	•
Throughfeed tank dishwashers	•
Washer-disinfectors, laboratory	•
Machine affiliation	
G 8066	•
PG 8067	•
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8063	•
PG 8164	•
PG 8165	•
PG 8166	•
PG 8169	•
PG 8172	•
PG 8172 Eco	•
PTD 901	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
PTD 701	•

E 313

Wall fitting

for the manual production of demineralized water.



EAN: 4002511115279 / Material number: 03830330 / Old Material Number: 69431301D

PTD 702	•
PTD 703	•
PTD 704	•
PG 8535	•
PG 8536	•
Product category	
Water treatment	•
Product characteristics	
Material	Plastic
Color	Black
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in inches	0 (0) in (mm)
External dimensions, net width in inches	0 (0) in (mm)
External dimensions, net depth in inches	0 (0) in (mm)
External dimensions, gross height in inches	7 11/16 (195)
External dimensions, gross width in inches	7 1/2 (190)
External dimensions, gross depth in inches	9 1/2 (240)
Net weight in lbs	3 (1.06)
Gross weight in lbs	3 (1.31)