

E 402

Mesh Basket

for optimum loading of up to 44 watch glasses.



- Suitable for 44 watch glasses Ø 80 – 125 mm
- Equipped with 23 bars spaced 0 5/8 (15) in (mm)

EAN: 4002511116627 / Material number: 03830420 / Old Material Number: 69540201D

<b>Product category</b>	
Washer-disinfectors, laboratory	•
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
G 7825	•
PG 8527	•
PG 8535	•
PG 8536	•
PG 8504	•
PG 8583	•
PG 8583 CD	•
PG 8593	•
PLW 8615	•
PLW 8616	•
PLW 8617	•
PLW 6011	•
PLW 6111	•
PLW 7111	•
PLW 8505	•
<b>Product category</b>	
Insert/module for watch glasses	•
<b>Product characteristics</b>	
Material	Stainless steel
Color	Stainless Steel
Distance between rails in mm	0 5/8 (15)
<b>Application area</b>	
Reprocessing of laboratory glassware	•
<b>Capacity</b>	
Watch glasses [number]	44
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
<b>Dimensions and weight</b>	
External dimensions, net height in inches	2 1/8 (53)
External dimensions, net width in inches	7 7/8 (200)
External dimensions, net depth in inches	17 9/16 (445)
External dimensions, gross height in inches	3 3/16 (80)
External dimensions, gross width in inches	8 11/16 (220)
External dimensions, gross depth in inches	17 3/4 (450)
Net weight in lbs	3 (0.92)
Gross weight in lbs	3 (1.14)