

E 403

Mesh Basket

for optimum loading of up to 105 watch glasses.



- Suitable for 105 watch glasses Ø 50 – 60 mm
- Equipped with 36 bars spaced 0 3/8 (9) in (mm)

EAN: 4002511116634 / Material number: 03830430 / Old Material Number: 69540301D

<b>Product category</b>	
Washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
G 7823	•
G 7825	•
G 7826	•
PG 8527	•
PG 8528	•
PG 8535	•
PG 8536	•
PG 8504	•
PG 8583	•
PG 8583 CD	•
PG 8593	•
PLW 8615	•
PLW 8616	•
PLW 8617	•
PLW 6011	•
PLW 6111	•
PLW 8505	•
<b>Product category</b>	
Insert/module for watch glasses	•
<b>Product characteristics</b>	
Material	Stainless steel
Color	Stainless Steel
Distance between rails in mm	0 3/8 (9)
<b>Application area</b>	
Reprocessing of laboratory glassware	•
<b>Capacity</b>	
Watch glasses [number]	105
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in inches	1 7/16 (35) in (mm)
External dimensions, net width in inches	7 7/8 (200) in (mm)
External dimensions, net depth in inches	17 9/16 (445) in (mm)
External dimensions, gross height in inches	3 (75)
External dimensions, gross width in inches	20 1/8 (510)
External dimensions, gross depth in inches	11 1/16 (280)
Net weight in lbs	3 (1.32)
Gross weight in lbs	4 (1.48)