


E 940

Mobile unit

for the optimum loading of narrow-neck glassware on 2 levels.



- The mobile injector unit can also be used without the upper level
- Magnetic strip for automatic mobile unit recognition
- Lower level equipped with a total of 15 nozzles with clips

EAN: 4002512145473 / Material number: 04607630 / Old Material Number: 69594001D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PG 8527	•
Product category	
Mobile unit for narrow-neck glassware	•
Product characteristics	
Material	Stainless steel, Plastic
Color	Stainless Steel, Black
Application area	
Reprocessing of laboratory glassware	•
Capacity	
Narrow-neck glassware [number]	115
Standard electrical connection	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
Dimensions and weight	
External dimensions, net height in inches	22 1/4 (565)
External dimensions, net width in inches	25 1/4 (640)
External dimensions, net depth in inches	31 1/8 (790)
External dimensions, gross height in inches	29 15/16 (760)
External dimensions, gross width in inches	31 1/2 (800)
External dimensions, gross depth in inches	47 1/4 (1200)
Net weight in lbs	78 (35.00)
Gross weight in lbs	100 (45.00)
Accessory pack	
Magnetic strip for automatic mobile unit recognition (incl. magnets) [number]	1