

E 815

Insert

For the optimum loading of glasses.



- Suitable for lower basket U 890
- For 10 tall beer glasses
- Rail height 9 1/2 (240) in (mm), distance between rails 3 3/4 (95) in (mm)

EAN: 4002512259446 / Material number: 05018670 / Old Material Number: 67581501D

Product category	
Fresh-water dishwashers	•
Machine affiliation	
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
Product category	
Insert for glasses	•
Product characteristics	
Material	Wire, rilsan-coated
Color	White
Distance between rails in mm	3 3/4 (95)
Rail height in mm	9 1/2 (240)
For use in lower basket	U 890
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0

E 815

Insert

For the optimum loading of glasses.



EAN: 4002512259446 / Material number: 05018670 / Old Material Number: 67581501D

Dimensions and weight	
External dimensions, net height in inches	252
External dimensions, net width in inches	220
External dimensions, net depth in inches	513
External dimensions, gross height in inches	9 7/8 (250)
External dimensions, gross width in inches	9 1/16 (230)
External dimensions, gross depth in inches	19 15/16 (505)
Net weight in lbs	4 (1.58)
Gross weight in lbs	5 (1.98)