

O 500

Upper basket

for the optimum loading of short, thin objects e.g. circuit boards



- Suitable for 37 circuit boards
- Equipped with 40 holders (2 13/16 (70) in (mm) mm high)
- Vertical clearance: 7 1/8 (180) in (mm) inches (mm)
- With integrated spray arm

EAN: 4002512431408 / Material number: 05376780 / Old Material Number: 69150001D

| Product category | |
|---|------------------------|
| Washer-disinfectors, laboratory | • |
| Machine affiliation | |
| IR 6002 | • |
| Product category | |
| Basket for cleaning industrial parts | • |
| Upper basket | • |
| Other baskets | • |
| Product characteristics | |
| Material | Wire, rilsan-coated |
| Color | White |
| Rail height in mm | 2 13/16 (70) |
| Maximum vertical clearance in mm | 7 1/8 (180) |
| Capacity | |
| Printed circuit boards [number] | 37 |
| Standard electrical connection | |
| Number of phases | 0 |
| Voltage in V | 0 |
| Frequency in Hz | 0 |
| Total rated load in kW | 0.00 |
| Fuse rating in A | 0 |
| Dimensions and weight | |
| External dimensions, net height in inches | 9 9/16 (242) in (mm) |
| External dimensions, net width in inches | 20 13/16 (528) in (mm) |
| External dimensions, net depth in inches | 18 3/4 (475) in (mm) |
| External dimensions, gross height in inches | 8 11/16 (220) |
| External dimensions, gross width in inches | 21 5/16 (540) |
| External dimensions, gross depth in inches | 20 7/8 (530) |
| Net weight in lbs | 10 (4.40) |
| Gross weight in lbs | 11 (4.80) |