


A 5

Lid

for optimum securing of delicate items.



- Stainl. steel frames w/ plastic netting (material quality PA 12)
- For use in O 184 and U 184

EAN: 4002513126310 / Material number: 05637190 / Old Material Number: 69500501D

| Product category                            |                                               |
|---------------------------------------------|-----------------------------------------------|
| Laboratory glasswashers                     | •                                             |
| Machine affiliation                         |                                               |
| G 7825                                      | •                                             |
| PG 8527                                     | •                                             |
| PG 8535                                     | •                                             |
| PG 8536                                     | •                                             |
| PLW 8636 [LAB / LAB MON]                    | •                                             |
| PG 8504                                     | •                                             |
| PG 8583                                     | •                                             |
| PG 8583 CD                                  | •                                             |
| PG 8593                                     | •                                             |
| PLW 8615                                    | •                                             |
| PLW 8616                                    | •                                             |
| PLW 8617                                    | •                                             |
| PLW 8683                                    | •                                             |
| PLW 8683 CD                                 | •                                             |
| PLW 8693                                    | •                                             |
| PLW 6011                                    | •                                             |
| PLW 6111                                    | •                                             |
| PLW 7111                                    | •                                             |
| PLW 8505                                    | •                                             |
| Product category                            |                                               |
| Cover                                       | •                                             |
| Application area                            |                                               |
| Reprocessing of laboratory glassware        | •                                             |
| Reprocessing of different utensils          | •                                             |
| Product characteristics                     |                                               |
| Material                                    | Stainless steel, Wire, rilsan-coated, Plastic |
| Color                                       | White                                         |
| Standard electrical connection              |                                               |
| Number of phases                            | 0                                             |
| Voltage in V                                | 0-0                                           |
| Frequency in Hz                             | 0-0                                           |
| Total rated load in kW                      | 0.00-0.00                                     |
| Fuse rating in A                            | 0-0                                           |
| Dimensions and weight                       |                                               |
| External dimensions, net height in inches   | 0 3/8 (8)                                     |
| External dimensions, net width in inches    | 11 1/16 (280)                                 |
| External dimensions, net depth in inches    | 11 1/16 (280)                                 |
| External dimensions, gross height in inches | 0 13/16 (20)                                  |
| External dimensions, gross width in inches  | 18 9/16 (470)                                 |
| External dimensions, gross depth in inches  | 18 9/16 (470)                                 |
| Net weight in lbs                           | 1 (0.40)                                      |
| Gross weight in lbs                         | 1 (0.55)                                      |