


E 752

Module

for the optimum loading of narrow neck- glassware 100 - 1,000 ml.



- With 12 nozzles (E 351) 4 x 160 mm with clips (E 353)
- With 13 nozzles (E 352) 6 x 220 mm with clips (E 354)

EAN: 4002513197471 / Material number: 05647640 / Old Material Number: 69575201D

<b>Product category</b>	
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
G 7825	•
G 7826	•
<b>Product category</b>	
Insert/module for narrow-neck glassware	•
<b>Product characteristics</b>	
Material	Stainless steel
Color	Stainless Steel
<b>Application area</b>	
Reprocessing of pipettes/vials	•
<b>Capacity</b>	
Narrow-neck glassware [number]	25
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
<b>Dimensions and weight</b>	
External dimensions, net height in inches	10 1/4 (260)
External dimensions, net width in inches	19 3/8 (492)
External dimensions, net depth in inches	19 9/16 (496)
External dimensions, gross height in inches	6 3/4 (170)
External dimensions, gross width in inches	20 7/8 (530)
External dimensions, gross depth in inches	22 1/16 (560)
Net weight in lbs	22 (9.70)
Gross weight in lbs	23 (10.00)