


E 950/1

Mobile unit

for the optimum loading of narrow-neck glassware on 3 levels.



- Equipped with 232 nozzles
- Levels 1+3: Each 80 nozzles ID 90 (2.5 x 90 mm)
- Level 2: 72 nozzles ID 90 (2.5 x 90 mm)
- Maximum vertical clearance on all three levels 148 mm each

EAN: 4002514072708 / Material number: 06696990 / Old Material Number: 69595002D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PG 8527	•
Product category	
Mobile unit for narrow-neck glassware	•
Product characteristics	
Material	Stainless steel, Plastic
Color	Stainless Steel, Black
Application area	
Reprocessing of laboratory glassware	•
Capacity	
Narrow-neck glassware [number]	232
Standard electrical connection	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
Dimensions and weight	
External dimensions, net height in inches	22 9/16 (572)
External dimensions, net width in inches	25 1/4 (640)
External dimensions, net depth in inches	31 1/8 (790)
External dimensions, gross height in inches	25 5/8 (650)
External dimensions, gross width in inches	25 5/8 (650)
External dimensions, gross depth in inches	32 5/16 (820)
Net weight in lbs	63 (28.20)
Gross weight in lbs	89 (40.00)
Accessory pack	
Magnetic strip for automatic mobile unit recognition (incl. magnets) [number]	1