

Printer
Report printer
for process documentation, integrated



- 8-wire matrix printer for process documentation
- Report creation and printing can be configured
- Can be installed on the operator side of the PG 8527
- Can be installed on the clean or unclean side of the PG 8528

EAN: 4002514111766 / Material number: 06758340 / Old Material Number: 69247001D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Large-capacity washer-disinfectors, medical	•
Machine affiliation	
PG 8527	•
PG 8528	•
Product category	
Other accessories	•
Standard electrical connection	
Number of phases	1
Neutral conductor	N
AC/DC	AC
Voltage in V	220-240
Frequency in Hz	50-60
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
Dimensions and weight	
External dimensions, gross height in inches	12 1/16 (305)
External dimensions, gross width in inches	11 13/16 (300)
External dimensions, gross depth in inches	7 7/8 (200)
Net weight in lbs	2 (0.90)
Gross weight in lbs	3 (1.00)