

Printer
Report printer
for process documentation, integrated



- 8-wire matrix printer for process documentation
- Report creation and printing can be configured
- Can be installed on the operator side of the PG 8527
- Can be installed on the clean or unclean side of the PG 8528

EAN: 4002514111766 / Material number: 06758340 / Old Material Number: 69247001D

| | |
|--|----------------|
| Product category | |
| Large-capacity washer-disinfectors, laboratory | • |
| Large-capacity washer-disinfectors, medical | • |
| Machine affiliation | |
| PG 8527 | • |
| PG 8528 | • |
| Product category | |
| Other accessories | • |
| Standard electrical connection | |
| Number of phases | 1 |
| Neutral conductor | N |
| AC/DC | AC |
| Voltage in V | 220-240 |
| Frequency in Hz | 50-60 |
| Total rated load in kW | 0.00-0.00 |
| Fuse rating in A | 0-0 |
| Dimensions and weight | |
| External dimensions, gross height in inches | 12 1/16 (305) |
| External dimensions, gross width in inches | 11 13/16 (300) |
| External dimensions, gross depth in inches | 7 7/8 (200) |
| Net weight in lbs | 2 (0.90) |
| Gross weight in lbs | 3 (1.00) |