

B 990
Rotary ironer
with high pressure and a wide heater plate for best results.



- No physical effort required thanks to high pressure
- Convenient ironing of large laundry pieces – wide heater plate
- Individual work speed thanks to variable roller speed
- Iron difficult laundry items easily – all-round free roller end

EAN: 4002514443676 / Material number: 07222730 / Old Material Number: 13099035USA

Design	
Appliance color	Lotus white
Perfect ironing results	
Temperature selection to suit textiles	•
High contact pressure in psi	0.51 (0.35)
Laundry feed board for easy laundry feed	•
Convenient infeed board with ample storage space	•
Airing bar for crease-free cooling	•
Time-saving ironing	
Roller length in in.(mm)	32 3/4 (830)
Variable roller speed	•
Moisture-absorbing roller padding	•
Control panel	
User convenience	
Effortless ironing while seated possible	•
Free, unsupported roller end	•
Clear control panel	•
Convenient folding mechanism	•
Easily maneuverable thanks to four castors	•
Safety	
Automatic finger guard	•
Emergency release	•
Good stability	•
Technical data	
Dimensions (width) in in. (mm)	38 7/8 (985)
Dimensions (height) in in.(mm)	37 7/8 (959)
Dimensions (depth) in in.(mm)	15 (380)
Dimensions (width), folded up in in.(mm)	19 3/4 (500)
Dimensions (height), folded up in in.(mm)	41 5/8 (1055)
Dimensions (depth), folded up in in.(mm)	15 (380)
Total connected load in kW	1.44
Frequency in Hz	60
Standard accessories	
Adhesive label for temperature selector	•