

E 900-5/2  
 Mobile unit  
 for the optimum cleaning of instruments on 5 levels.



- Loading capacity: 15 DIN mesh trays\*
- The loading areas for the individual levels are different
- Magnetic strip for mobile unit recognition (incl. magnets ML)

\* DIN mesh tray 485 x 254 x 50 mm

EAN: 4002514816418 / Material number: 07765760 / Old Material Number: 69590006D

|   |                 |
|---|-----------------|
| <b>Product category</b>   |                 |
| Large-capacity washer-disinfectors, laboratory                                | •               |
| Washer-disinfectors, medical  | •               |
| <b>Machine affiliation</b>  |                 |
| PG 8527   | •               |
| PG 8528   | •               |
| <b>Product category</b>   |                 |
| Mobile unit for inserts   | •               |
| Mobile unit for mesh trays  | •               |
| <b>Product characteristics</b>  |                 |
| Material  | Stainless steel |
| Color   | Stainless Steel |
| <b>Application area</b>   |                 |
| Reprocessing of laboratory glassware  | •               |
| Reprocessing of surgical instruments  | •               |
| <b>Capacity</b>   |                 |
| DIN mesh trays [number]   | 15              |
| SPRI mesh trays [number]  | 10              |
| <b>Standard electrical connection</b>   |                 |
| Number of phases  | 0               |
| Voltage in V  | 0-0             |
| Frequency in Hz   | 0-0             |
| Total rated load in kW  | 0.00-0.00       |
| Fuse rating in A  | 0-0             |
| <b>Dimensions and weight</b>  |                 |
| External dimensions, net height in inches                                     | 23 7/8 (605)    |
| External dimensions, net width in inches                                      | 25 1/4 (640)    |
| External dimensions, net depth in inches                                      | 31 1/8 (790)    |
| External dimensions, gross height in inches                                   | 26 13/16 (680)  |
| External dimensions, gross width in inches                                    | 22 1/16 (560)   |
| External dimensions, gross depth in inches                                    | 25 5/8 (650)    |
| Net weight in lbs   | 29 (12.85)      |
| Gross weight in lbs   | 29 (12.85)      |
| <b>Accessory pack</b>   |                 |
| Magnetic strip for automatic mobile unit recognition (incl. magnets) [number] | 1               |