

PT 7186 Vario [EL]

Vented dryer, electric heating

with a shortest program runtime of 37 min for a high laundry throughput.



- Drum volume 6.36 (180.00) ft³ (l), load size 18 (8.0) lb (kg)
- Large program variety – application-specific drying programs
- Precision drying of all fabrics – PerfectDry
- Unique, gentle fabric care – patented honeycomb drum
- Easy operation – viewing window and large-surface filter

EAN: 4002515128718 / Material number: 09294650 / Old Material Number: 52718663USA

| Model and design | |
|-----------------------------------------------------------|------------------------------|
| Design | Front loader |
| Linie | Octoplus |
| Front | Octo blue |
| Load in lbs.(kg) | 18 (8.0) |
| Fill ratio | 1:22,5 |
| Drum volume in ft ³ (l) | 6.36 (180.00) |
| Drying system | Exhaust air |
| Door opening [Ø] in in.(mm) | 17 3/8 (440) |
| Door opening angle in degrees | 180 |
| Door hinging | left |
| Stainless steel honeycomb drum | Yes |
| Application | |
| Suitable for the hotel and catering industry | • |
| Suitable for retirement and care homes | • |
| Suitable for facility management | • |
| Suitable for dry cleaners | • |
| Suitable for commercial laundries | • |
| Suitable for small businesses | • |
| Suitable for fire brigades and rescue services | • |
| Suitable for studs, riding schools and stables | • |
| Suitable for universities, nurseries, and schools | • |
| Suitable for hospitals | • |
| Suitable for sports clubs | • |
| Suitable for beauty salons, spas and fit ness centers | • |
| Suitable for doctors' and dentists' practices | • |
| Performance data | |
| Maximum evaporation capacity in l/hour and gal. qts./hour | 8.10 |
| Program cycle in min. | 37 |
| Controls | |
| Control system | Profitronic L Vario |
| Programmability | programmable |
| Program controls | Residual moisture controlled |
| Max. delay start in h | 24 |
| Countdown indicator | • |
| Program sequence indicator | • |
| Fascia panel with clear text | • |
| Choice of display language | • |
| Standard/target group programs | |
| Basic programmes | • |
| Programmes for facility management | • |
| Programmes for dry cleaners | • |
| Programmes for fire brigades and rescue services | • |
| Programmes for studs, riding schools, and stables | • |
| Programmes for domestic use | • |
| Standard electrical connection | |
| Type of heating | Electric |
| Electrical connection | 2 AC 208V 60HZ |
| Electric heater rating in kW | 4.34 |

PT 7186 Vario [EL]

Vented dryer, electric heating

with a shortest program runtime of 37 min for a high laundry throughput.



EAN: 4002515128718 / Material number: 09294650 / Old Material Number: 52718663USA

| | |
|------------------------------------------------|---------------------|
| Total connected load in kW | 4.84 |
| Fuse rating in A | 30 |
| NEMA plug: Twist Lock L6-30 | • |
| Dimensions and weight | |
| External dimensions, net height in inches | 40 3/16 (1020) |
| External dimensions, net width in inches | 27 9/16 (700) |
| External dimensions, net depth in inches | 30 1/16 (763) |
| External dimensions, gross height in inches | 47 7/8 (1215) |
| External dimensions, gross width in inches | 29 15/16 (760) |
| External dimensions, gross depth in inches | 32 5/16 (820) |
| Net weight in lbs. (kg) | 170 (77.0) |
| Gross weight in lbs. (kg) | 195 (88) |
| Maximum floor loading in N | 1000 |
| Emissions data | |
| Emissions – sound pressure at workplace | <70 dB(A) re 20 µPa |
| Heat output to the room in MJ/h and BTUs /h | 1.62 |
| Features | |
| Intelligent drum reversal | • |
| Axial airflow | • |
| Large-surface filter | • |
| PerfectDry | • |
| SoftLift drum ribs | • |
| Low temperature function | • |
| Communication slot | • |
| Drying basket (optional) | • |
| Machine-independent accessories | • |
| Connection options | |
| Payment system | • |
| Serial interface RS 232 (optional) | • |
| Optical interface for service access | • |
| Peak load cut-out/energy management (optional) | • |
| Capacities | |
| Respirator masks [number] | 4 |
| Standard and target group programs | 1-2 |
| Over jackets [number] | 1-2 |
| Synthetic duvets [number] | 1 |
| Synthetic pillows [number] | 1-2 |
| Feather duvets [number] | 1 |
| Feather pillows [number] | 1-2 |
| Cloths, 22 g/0.8 oz [number] | 182 |
| Cotton mops, 40 cm [number] | 42 |
| Cotton mops, 50 cm [number] | 36 |
| Microfibre mops, 40 cm [number] | 66 |
| Microfibre mops, 50 cm [number] | 47 |
| Summer horse blankets [number] | 1-2 |
| Standards/certificates/symbols | |
| Splash-proof safety rating IPX4 | • |
| Complies with Machinery Directive 2006/42/EC | • |