

PT 7186 Vario [EL]

Vented dryer, electric heating

with a shortest program runtime of 37 min for a high laundry throughput.



- Drum volume 6.36 (180.00) ft³ (l), load size 18 (8.0) lb (kg)
- Large program variety – application-specific drying programs
- Precision drying of all fabrics – PerfectDry
- Unique, gentle fabric care – patented honeycomb drum
- Easy operation – viewing window and large-surface filter

EAN: 4002515128725 / Material number: 09294670 / Old Material Number: 52718666USA

Construction type and design	
Design	Front loader
Linie	Octoplus
Front	Octo Blue
Load in lbs.(kg)	18 (8.0)
Fill ratio	1:22,5
Drum volume in ft ³ (l)	6.36 (180.00)
Drying system	Exhaust air
Door opening [Ø] in.in.(mm)	17 3/8 (440)
Door opening angle in degrees	180
Door hinging	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas and fit ness centers	•
Suitable for doctors' and dentists' practices	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	8.10
Program cycle in min.	37
Control	
Control system	Profitronic L Vario
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Standard/target group programs	
Basic programmes	•
Programmes for facility management	•
Programmes for dry cleaners	•
Programmes for fire brigades and rescue services	•
Programmes for studs, riding schools, and stables	•
Programmes for domestic use	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	2 AC 240V 60HZ
Electric heater rating in kW	5.20
Total connected load in kW	5.70

PT 7186 Vario [EL]

Vented dryer, electric heating

with a shortest program runtime of 37 min for a high laundry throughput.



EAN: 4002515128725 / Material number: 09294670 / Old Material Number: 52718666USA

Fuse rating in A	30
NEMA plug: Twist Lock L6-30	•
Dimensions and weight of dryer	
External dimensions, net height in inches	40 3/16 (1020)
External dimensions, net width in inches	27 9/16 (700)
External dimensions, net depth in inches	30 1/16 (763)
External dimensions, gross height in inches	47 7/8 (1215)
External dimensions, gross width in inches	29 15/16 (760)
External dimensions, gross depth in inches	32 5/16 (820)
Net weight in lbs. (kg)	170 (77.0)
Gross weight in lbs. (kg)	195 (88)
Maximum floor load in N/m ²	1000
Emission values	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	1.62
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drying basket (optional)	•
Machine-independent accessories	•
Connection options	
Payment system	•
Serial interface RS 232 (optional)	•
Optical interface for service access	•
Peak-load negotiation/energy management (optional)	•
Capacities	
Respirator masks [number]	4
Standard and target group programs	1
Over jackets [number]	1-2
Synthetic duvets [number]	1
Synthetic pillows [number]	1-2
Feather duvets [number]	1
Feather pillows [number]	1-2
Cloths, 22 g/0.8 oz [number]	182
Cotton mops, 40 cm [number]	42
Cotton mops, 50 cm [number]	36
Microfibre mops, 40 cm [number]	66
Microfibre mops, 50 cm [number]	47
Summer horse blankets [number]	1-2
Standards, test certificates, and symbols	
Splash-proof safety rating IPX4	•
Complies with Machinery Directive 2006/42/EC	•