

U 890

Lower basket

Without inserts for individual loading options.



- For holding inserts or baskets up to 19.7 x 19.7 inches

EAN: 4002515274989 / Material number: 09549130 / Old Material Number: 67189001D

| | |
|---|---------------------|
| Product category | |
| Fresh-water dishwashers | • |
| Machine affiliation | |
| PG 8041 | • |
| PG 8043 | • |
| PG 8045 | • |
| PG 8055 | • |
| PG 8055 U | • |
| PG 8056 | • |
| PG 8056 U | • |
| PG 8057 TD | • |
| PG 8057 TD U | • |
| PG 8058 | • |
| PG 8058 U | • |
| PG 8059 | • |
| PG 8059 U | • |
| PG 8060 | • |
| PG 8061 | • |
| PG 8061 U | • |
| PG 8096 | • |
| PG 8096 U | • |
| PG 8099 | • |
| PG 8099 U | • |
| PFD 400 | • |
| PFD 400 U | • |
| PFD 401 | • |
| PFD 401 U | • |
| PFD 402 | • |
| PFD 402 U | • |
| PFD 404 | • |
| PFD 404 U | • |
| PFD 405 | • |
| PFD 405 U | • |
| PFD 407 | • |
| PFD 407 U | • |
| PFD 408 U | • |
| Product category | |
| Lower basket | • |
| Product characteristics | |
| Material | Wire, rilsan-coated |
| Color | White |
| Standard electrical connection | |
| Number of phases | 0 |
| Voltage in V | 0 |
| Frequency in Hz | 0 |
| Total rated load in kW | 0.00 |
| Fuse rating in A | 0 |
| Dimensions and weight | |
| External dimensions, net height in inches | 100 |
| External dimensions, net width in inches | 532 |

U 890

Lower basket

Without inserts for individual loading options.



EAN: 4002515274989 / Material number: 09549130 / Old Material Number: 67189001D

| | |
|---|---------------|
| External dimensions, net depth in inches | 517 |
| External dimensions, gross height in inches | 4 15/16 (125) |
| External dimensions, gross width in inches | 21 7/8 (555) |
| External dimensions, gross depth in inches | 21 7/8 (555) |
| Net weight in lbs | 6 (2.50) |
| Gross weight in lbs | 7 (3.00) |