

KFN 9855 iDE

PerfectCool fridge-freezer

maximum convenience thanks to generous large capacity and ice maker.



- Optimum and maintenance-free LED lighting in compartment
- Store food anywhere in the refrigerator – Dynamic cooling
- No icing up of food and no need to defrost thanks to Frost free
- Ice cubes thanks to the plumbed IceMaker
- Door shelves can be cleaned in the dishwasher – ComfortClean

EAN: 4002515318911 / Material number: 09623660 / Old Material Number: 38985552CDN

<b>Appliance category</b>	
Fridge-freezer	•
<b>Design</b>	
Built-in	•
Built-in integrated	•
Door hinge side	Left
<b>Design</b>	
Type of lighting	LED
<b>User convenience</b>	
ComfortClean	•
DynaCool	•
NoFrost	•
DuplexCool	•
SoftClose door closing damper	•
IceMaker with plumbed water connection	•
<b>Control</b>	
Fridge compartment can be switched off	Yes
Independent temperature control of fridge and freezer compartments	No
Super Cooling	•
No. of temperature zones	2
<b>Fridge/fridge zone</b>	
No. of shelves	3
Chrome-plated metal bottle rack	•
Number of door racks for cans	2
Door rack for bottles	1
<b>Freezer/freezer zone</b>	
Number of freezer drawers	2
<b>Efficiency and sustainability</b>	
Energy Star Qualified	•
<b>Safety</b>	
Optical door alarm	•
Optical temperature alarm	•
Power cut indication for freezer compartment	•
<b>Technical data</b>	
Niche width in inches (mm), min.	30 (762)
Niche width in inches (mm), max.	30 (762)
Niche height in inches (mm), min.	80 (2032)
Niche height in inches (mm), max.	81 5/8 (2072)
Niche depth in in.(mm)	24 1/8 (610)
Appliance width in in.(mm)	29 7/8 (757)
Appliance height in in.(mm)	79 3/4 (2024)
Appliance depth in in.(mm)	24 1/8 (610)
Weight in lbs.(kg)	320 (145.0)
Type of mounting	Fixed door
Climatic classification	SN-T
Total usable capacity in cu. ft. (l)	14.13 (400)
Storage time in case of fault in h	30
Current consumption in milliampere (mA)	2500
Voltage in V	115

KFN 9855 iDE

PerfectCool fridge-freezer

maximum convenience thanks to generous large capacity and ice maker.

EAN: 4002515318911 / Material number: 09623660 / Old Material Number: 38985552CDN




Fuse rating in A	10
Number of phases	1
Frequency in Hz	60
Wire length in ft (m)	9 (2.8)
Replacing bulbs	Customer Service

KFN 9855 iDE

PerfectCool fridge-freezer

maximum convenience thanks to generous large capacity and ice maker.



KFN9855iDE, KFN9855iDE with footnote\* (installation drawings)

\* A = 3" ( 76 mm), B = 79- 13/16" ( 2027 mm), C = 29- 7/8" ( 757 mm), D = 24" ( 610 mm), E = 55 1/4" ( 1413 mm), F = 37- 1/8" ( 952 mm)