

UO 52-60/80

Plinth, open

For the ergonomic loading and unloading of a dishwasher - height 52 cm.



- Suitable for fresh water systems (PG 8056 and PG 8061)
- Can be mounted on to the dishwasher
- Height 52, width 60, depth 60 cm

EAN: 4002515362693 / Material number: 09688900 / Old Material Number: 67376107D

| Product category | |
|---|-----------------|
| Fresh-water dishwashers | • |
| Tank dishwashers | • |
| Machine affiliation | |
| G 8066 | • |
| PG 8067 | • |
| PG 8041 | • |
| PG 8043 | • |
| PG 8045 | • |
| PG 8055 | • |
| PG 8055 U | • |
| PG 8056 | • |
| PG 8056 U | • |
| PG 8057 TD | • |
| PG 8057 TD U | • |
| PG 8058 | • |
| PG 8058 U | • |
| PG 8059 | • |
| PG 8059 U | • |
| PG 8060 | • |
| PG 8061 | • |
| PG 8061 U | • |
| PG 8063 | • |
| PG 8096 | • |
| PG 8099 | • |
| PFD 400 | • |
| PFD 401 | • |
| PFD 402 | • |
| PFD 404 | • |
| PFD 405 | • |
| PFD 407 | • |
| Product category | |
| Open plinth | • |
| Product characteristics | |
| Material | Stainless steel |
| Color | Stainless Steel |
| Standard electrical connection | |
| Number of phases | 0 |
| Voltage in V | 0-0 |
| Frequency in Hz | 0-0 |
| Total rated load in kW | 0.00-0.00 |
| Fuse rating in A | 0-0 |
| Dimensions and weight | |
| External dimensions, net height in inches | 21 3/16 (537) |
| External dimensions, net width in inches | 23 5/8 (600) |
| External dimensions, net depth in inches | 23 5/8 (600) |
| External dimensions, gross height in inches | 12 1/4 (310) |
| External dimensions, gross width in inches | 24 1/16 (610) |
| External dimensions, gross depth in inches | 24 1/16 (610) |
| Net weight in lbs | 18 (7.87) |
| Gross weight in lbs | 23 (10.07) |

UO 52-60/80

Plinth, open

For the ergonomic loading and unloading of a dishwasher - height 52 cm.