

## PG 8056-1 U [240V]

Built-under fresh water dishwasher

ADA compliant, with baskets for hotels, restaurants and catering companies.



- Max. cleaning performance\*: 380 plates/h or 20 baskets/h
- Flexible processing of two wire or plastic baskets per cycle
- Simple to operate thanks to clear fascia panel design
- Always the right program – item-specific solutions
- First-class results thanks to fresh water system

\* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

EAN: 4002515460870 / Material number: 09862610 / Old Material Number: 61805655USA

Construction type and design	
Model	Built-under dishwasher
Range	Professional
Wash system	Fresh water front loader
Number of levels	2
Front	Stainless steel
Lid	Stainless Steel
Side walls	Stainless steel
Convertible to a freestanding appliance	Stand 1-80, stainless steel
Application	
Suitable for small restaurants/bars	•
Suitable for hospitality industry	•
Suitable for Bed & Breakfast	•
Suitable for canteens	•
Suitable for small businesses	•
Suitable for fast food restaurants	•
Suitable for sports clubs	•
Performance data	
Circulation pump, Qmax in gal/min (l/min)	103 (390)
Shortest program duration in min.	6
Maximum final rinse temperature in °F (°C)	158 (70)
Cleaning performance, plates/h	380
Cleaning performance, baskets/h	20
Possible to wash plastic baskets on two levels	•
Service life in wash cycles	15000
Control	
Control system	TouchControl
Program selection	Touch on Metal
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Language-neutral operation	•
Standard electrical connection	
Electrical connection	2 PH. 240V 60HZ
Heater rating in kW	5.40
Total connected load in kW	5.80
Fuse rating in A	30
Length of power cord in ft (m)	7 (2.20)
Possible voltage variant 1	
Electrical connection	3 PH. 240V 60HZ
Heater rating in kW	5.40
Total connected load in kW	5.80
Fuse rating in A	20
Water connection/drainage	
Cold water [number]	1
Hot water [number]	1
Required flow pressure in bar	0.40-10.00
Drain hose [DN]	22
Maximum delivery head for drain pump in inches (cm)	39 3/8 (100)

PG 8056-1 U [240V]

Built-under fresh water dishwasher

ADA compliant, with baskets for hotels, restaurants and catering companies.



EAN: 4002515460870 / Material number: 09862610 / Old Material Number: 61805655USA

Integrated water softener	•
Maximum water hardness in gpg (mmol/l)	62.59 (10.70)
Water consumption per wash cycle in gal (l)	2.1 (8.00) gll (l)
<b>Dimensions and weight</b>	
External dimensions, net height in inches	32 5/16 (820)
External dimensions, net width in inches	23 9/16 (598)
External dimensions, net depth in inches	22 7/8 (580)
External dimensions, gross height in inches	37 1/16 (940)
External dimensions, gross width in inches	26 5/8 (675)
External dimensions, gross depth in inches	29 3/8 (745)
Usable space in wash cabinet, width in inches (mm)	22 1/16 (559)
Usable space in wash cabinet, height in inches (mm)	20 7/8 (530)
Usable space in wash cabinet, depth of upper basket in inches (mm)	18 11/16 (474)
Usable space in wash cabinet, depth of lower basket in inches (mm)	19 15/16 (505)
In-feed height above floor in inches (mm)	8 9/16 (216)
Net weight [kg]	139 (63)
Gross weight in lbs.	153 (69)
Maximum floor load in N/m <sup>2</sup>	1200
<b>Emission values</b>	
Emission sound pressure level in workplace (LpA)	47 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	59.0
Heat output to the room in MJ/h	1.08
<b>Baskets</b>	
1 x O 891 upper basket for cups	•
1 x U 890 lower basket for inserts	•
1 x E 810 insert for dessert plates	•
2 x E 816 inserts for plates	•
2 x E 165 inserts for cutlery	•
Height-adjustable upper basket	•
<b>Features</b>	
Drying	None
1 Combi dispenser/door for powder and liquid media	•
Wash cabinet made from high-quality stainless steel	•
In-door salt container	•
Perfect GlassCare	•
Adjustable temperature holding time	•
Adjustable final rinse temperature	•
Adjustable wash temperature	•
Adjustable rinse time	•
Optical interface	•
A wide range of accessories (optional)	•
<b>Connection options</b>	
External dispensing module for liquid cleaning agent	•
<b>Standards, test certificates, and symbols</b>	
CE	•
Complies with Machinery Directive 2006/42/EC	•
EMC	•
Interference suppression	•
VDE	•

PG 8056-1 U [240V]

Built-under fresh water dishwasher

ADA compliant, with baskets for hotels, restaurants and catering companies.



EAN: 4002515460870 / Material number: 09862610 / Old Material Number: 61805655USA

DIN 10512

EN 1717

ADA compliant

•

•

•