

## PT 8507 [PTM EL BSS ARP]

Vented dryer, electric heating

With individually programmable controls for the maximum in flexibility.



- Drum volume 17.66 (500.00) ft<sup>3</sup> (l), load size ??
- Unique, gentle fabric care – patented honeycomb drum
- Greatest energy efficiency thanks to Air Recycling Plus
- Precision drying of all fabrics – PerfectDry
- Simple operation – easy to clean large fluff filter

EAN: 4002515480960 / Material number: 09906730 /

Old Material Number: 52850705USA

| Construction type and design                              |                              |
|---|------------------------------|
| Design  | Front loader                 |
| Linie   | Professional                 |
| Front   | Stainless Steel              |
| Fill ratio  | 1:25-1:20                    |
| Drum volume in ft <sup>3</sup> (l)                        | 17.66 (500.00)               |
| Drying system   | Exhaust air                  |
| Door opening [Ø] in in.(mm)                               | 20 1/2 (520)                 |
| Door opening angle in degrees                             | 180                          |
| Door hinging  | left                         |
| Convertible hinging                                       | •                            |
| Stainless steel honeycomb drum                            | Yes                          |
| Application   |                              |
| Suitable for the hotel and catering industry              | •                            |
| Suitable for retirement and care homes                    | •                            |
| Suitable for facility management                          | •                            |
| Suitable for dry cleaners                                 | •                            |
| Suitable for commercial laundries                         | •                            |
| Suitable for fire brigades and rescue services            | •                            |
| Suitable for studs, riding schools and stables            | •                            |
| Suitable for universities, nurseries, and schools         | •                            |
| Suitable for hospitals                                    | •                            |
| Suitable for sports clubs                                 | •                            |
| Suitable for beauty salons, spas and fit ness centers     | •                            |
| Performance data  |                              |
| Maximum evaporation capacity in l/hour and gal. qts./hour | 26.80                        |
| Program cycle in min.                                     | 24                           |
| Tested operating hours                                    | 20000                        |
| Control   |                              |
| Control system  | Profitronic M                |
| Programmability   | Freely programmable          |
| Program controls  | Residual moisture controlled |
| Max. delay start in h                                     | Can be selected freely       |
| Countdown indicator                                       | •                            |
| Program sequence indicator                                | •                            |
| Choice of display language                                | •                            |
| Standard/target group programs                            |                              |
| Basic programmes  | •                            |
| Programmes for the hotel and catering industry            | •                            |
| Programmes for retirement and care homes                  | •                            |
| Programmes for facility management                        | •                            |
| Programmes for dry cleaners                               | •                            |
| Programmes for fire brigades and rescue services          | •                            |
| Programmes for studs, riding schools, and stables         | •                            |
| Standard electrical connection                            |                              |
| Type of heating   | Electric                     |
| Electrical connection                                     | 3 AC 220-240V 60HZ           |

## PT 8507 [PTM EL BSS ARP]

Vented dryer, electric heating

With individually programmable controls for the maximum in flexibility.



EAN: 4002515480960 / Material number: 09906730 /

Old Material Number: 52850705USA

|                              |             |
|------------------------------|-------------|
| Electric heater rating in kW | 24.70-29.40 |
| Total connected load in kW   | 26.00-30.70 |
| Fuse rating in A             | 80          |

### Possible voltage variant 1

|                            |                |
|----------------------------|----------------|
| Electrical connection      | 3 AC 208V 60HZ |
| Heater rating in kW        | 22.10          |
| Total connected load in kW | 23.40          |
| Fuse rating in A           | 80             |

### Dimensions and weight of dryer

|   |                |
|---|----------------|
| External dimensions, net height in inches   | 64 5/8 (1640)  |
| External dimensions, net width in inches    | 47 1/2 (1206)  |
| External dimensions, net depth in inches    | 40 1/8 (1018)  |
| External dimensions, gross height in inches | 69 9/16 (1766) |
| External dimensions, gross width in inches  | 54 3/4 (1390)  |
| External dimensions, gross depth in inches  | 58 1/16 (1474) |
| Net weight in lbs. (kg)                     | 633 (287.0)    |
| Gross weight in lbs. (kg)                   | 739 (335)      |
| Maximum floor load in N                     | 2703           |

### Emission values

|   |                     |
|---|---------------------|
| Emissions – sound pressure at workplace | ≤70 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h  | 3.25                |

### Features

|                                 |   |
|---------------------------------|---|
| Intelligent drum reversal       | • |
| Axial airflow                   | • |
| Large-surface fluff filter      | • |
| PerfectDry                      | • |
| SoftLift drum ribs              | • |
| AirRecyclingPlus                | • |
| Low temperature function        | • |
| Communication slot              | • |
| Emergency shut off              | • |
| Machine-independent accessories | • |

### Connection options

|   |   |
|---|---|
| Payment system (optional)                 | • |
| Serial interface RS 232 (optional)        | • |
| Optical interface for service access      | • |
| Peak-load negotiation / energy management | • |
| Operating data acquisition                | • |

### Capacities

|                                    |     |
|------------------------------------|-----|
| Respirator masks [number]          | 12  |
| Standard and target group programs | 3-4 |
| Over jackets [number]              | 5   |
| Synthetic duvets [number]          | 2   |
| Synthetic pillows [number]         | 5   |
| Feather duvets [number]            | 2   |
| Feather pillows [number]           | 5   |
| Cloths, 22 g/0.8 oz [number]       | 460 |
| Cotton mops, 40 cm [number]        | 105 |

PT 8507 [PTM EL BSS ARP]  
Vented dryer, electric heating  
With individually programmable controls for the maximum in flexibility.



EAN: 4002515480960 / Material number: 09906730 /  
Old Material Number: 52850705USA

|                                 |     |
|---------------------------------|-----|
| Cotton mops, 50 cm [number]     | 91  |
| Microfibre mops, 40 cm [number] | 167 |
| Microfibre mops, 50 cm [number] | 118 |
| Summer horse blankets [number]  | 3   |

|  |   |
|--|---|
| Standards, test certificates, and symbols    |   |
| CE   | • |
| Splash-proof safety rating IPX4              | • |
| Complies with Machinery Directive 2006/42/EC | • |