

PT 8507 [PTM EL BSS ARP]

Vented dryer, electric heating

With individually programmable controls for the maximum in flexibility.



- Drum volume 17.66 (500.00) ft³ (l) 17.66 (500.00) ft³ (l), load capacity 20.0-25.0 kg
- Unique, gentle fabric care – patented honeycomb drum
- Greatest energy efficiency thanks to Air Recycling Plus
- Precision drying of all fabrics – PerfectDry
- Simple operation – easy to clean large fluff filter

EAN: 4002515480960 / Material number: 09906730 / Old Material Number: 52850705USA

Construction type and design	
Design	Front loader
Linie	Professional
Front	Stainless steel
Load in lbs.(kg)	20.0-25.0
Fill ratio	1:25-1:20
Drum volume in gal(l)	17.66 (500.00)
Drying system	Vented
Door opening [Ø] in.in.(mm)	20 1/2 (520)
Door opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas and fit ness centers	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	26.80
Program cycle in min.	24
Tested operating hours	20000
Controls	
Control system	Profitronic M
Programmability	Freely programmable
Program controls	Residual moisture controlled
Max. delay start in h	Freely selectable
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Standard and target group Programmes	
Basic programmes	•
Programmes for the hotel and catering industry	•
Programmes for retirement and care homes	•
Programmes for facility management	•
Programmes for dry cleaners	•
Programmes for fire brigades and rescue services	•
Programmes for studs, riding schools, and stables	•
Standard electrical connection	
Type of heating	Electrical
Electrical connection	3 AC 220-240V 60HZ
Electric heater rating in kW	24.70-29.40

PT 8507 [PTM EL BSS ARP]

Vented dryer, electric heating

With individually programmable controls for the maximum in flexibility.



EAN: 4002515480960 / Material number: 09906730 / Old Material Number: 52850705USA

Total connected load in kW	26.00-30.70
Fuse rating in A	80
Possible voltage variant 1	
Electrical connection	3 AC 208V 60HZ
Heater rating in kW	22.10
Total connected load in kW	23.40
Fuse rating in A	80
Dimensions and weight	
External dimensions, net height in inches	64 5/8 (1640)
External dimensions, net width in inches	47 1/2 (1206)
External dimensions, net depth in inches	40 1/8 (1018)
External dimensions, gross height in inches	69 5/8 (1766)
External dimensions, gross width in inches	54 3/4 (1390)
External dimensions, gross depth in inches	58 1/8 (1474)
Net weight in lbs. (kg)	633 (287.0)
Gross weight in lbs. (kg)	739 (335)
Maximum floor loading in N	2703
Emission levels	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat output to the room in MJ/h and BTUs /h	3.25
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecyclingPlus	•
Low temperature function	•
Communication slot	•
Emergency shut off	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Serial interface RS 232 (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management	•
Operating data acquisition	•
Capacities	
Respirator masks [number]	12
Standard and target group programs	3-4
Over jackets [number]	5
Synthetic duvets [number]	2
Synthetic pillows [number]	5
Feather duvets [number]	2
Feather pillows [number]	5
Cloths, 22 g/0.8 oz [number]	460
Cotton mops, 40 cm [number]	105
Cotton mops, 50 cm [number]	91
Microfibre mops, 40 cm [number]	167
Microfibre mops, 50 cm [number]	118
Summer horse blankets [number]	3

PT 8507 [PTM EL BSS ARP]

Vented dryer, electric heating

With individually programmable controls for the maximum in flexibility.



EAN: 4002515480960 / Material number: 09906730 / Old Material Number: 52850705USA

Test certificate	
CE	•
Splash-proof safety rating IPX4	•
Complies with Machinery Directive 2006/42/EC	•