

## PT 8407 HW [PTM ARP]

Vented dryer, heated with hot water

With individually programmable controls and future-oriented heating method.



- Drum volume 14.13 (400.00) ft<sup>3</sup> (l), load size 13.0-16.0 kg
- Unique, gentle fabric care – patented honeycomb drum
- Greatest energy efficiency thanks to Air Recycling Plus
- Precision drying of all fabrics – PerfectDry
- Highest efficiency thanks to innovative hot water heating

EAN: 4002515527924 / Material number: 09984490 / Old Material Number: 52840775USA

Model and design	
Design	Front loader
Linie	Professional
Front	Stainless steel
Load in lbs.(kg)	13.0-16.0
Fill ratio	1:32-1:25
Drum volume in ft <sup>3</sup> (l)	14.13 (400.00)
Drying system	Hot water
Door opening [Ø] in in.(mm)	20 1/2 (520)
Door opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas and fit ness centers	•
Performance data	
Program cycle in min.	51
Tested operating hours	20000
Controls	
Control system	Profitronic M
Programmability	Freely programmable
Program controls	Residual moisture controlled
Max. delay start in h	Can be selected freely
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Standard/target group programs	
Basic programmes	•
Programmes for the hotel and catering industry	•
Programmes for retirement and care homes	•
Programmes for facility management	•
Programmes for dry cleaners	•
Programmes for fire brigades and rescue services	•
Programmes for studs, riding schools, and stables	•
Standard electrical connection	
Type of heating	Hot water
Electrical connection	3 AC 208V 60HZ
Electric heater rating in kW	0.00
Heater rating, hot water in kW	9.80

PT 8407 HW [PTM ARP]

Vented dryer, heated with hot water

With individually programmable controls and future-oriented heating method.



EAN: 4002515527924 / Material number: 09984490 / Old Material Number: 52840775USA

Total connected load in kW	1.30
Fuse rating in A	10
Minimum water intake temperature in °F	70
Maximum water intake temperature in °F	90
Volume in m <sup>3</sup> /h	0.3-1.5
<b>Possible voltage variant 1</b>	
Electrical connection	3 AC 220-240V 60HZ
Heater rating in kW	0.00
Total connected load in kW	1.30
Fuse rating in A	10
<b>Dimensions and weight</b>	
External dimensions, net height in inches	55 1/8 (1400)
External dimensions, net width in inches	35 11/16 (906)
External dimensions, net depth in inches	45 7/8 (1164)
External dimensions, gross height in inches	60 1/8 (1526)
External dimensions, gross width in inches	42 15/16 (1090)
External dimensions, gross depth in inches	49 3/8 (1254)
Net weight in lbs. (kg)	478 (216.5)
Gross weight in lbs. (kg)	530 (240)
Maximum floor loading in N	2348
<b>Emissions data</b>	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	2.64
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecyclingPlus	•
Low temperature function	•
Communication slot	•
Emergency shut off	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Serial interface RS 232 (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
Operating data acquisition	•
<b>Capacities</b>	
Respirator masks [number]	16
Standard and target group programs	3
Over jackets [number]	4
Synthetic duvets [number]	2
Synthetic pillows [number]	4
Feather duvets [number]	2
Feather pillows [number]	4
Cloths, 22 g/0.8 oz [number]	370
Cotton mops, 40 cm [number]	84
Cotton mops, 50 cm [number]	73

PT 8407 HW [PTM ARP]

Vented dryer, heated with hot water

With individually programmable controls and future-oriented heating method.



EAN: 4002515527924 / Material number: 09984490 / Old Material Number: 52840775USA

Microfibre mops, 40 cm [number]	133
Microfibre mops, 50 cm [number]	94
Summer horse blankets [number]	2-3
<b>Standards/certificates/symbols</b>	
CE	•
VDE	•
Splash-proof safety rating IPX4	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•