

PG 8595

Aqua purificator

for two full or partial demineralization cartridges.



- Suitable for VE/TE P 2800 & VE/TE P 2000
- Suitable for VE/TE P 2800 & VE/TE P 2000
- Possible to hold conductivity meter/flow meter
- Possible to hold conductivity meter/flow meter
- Ext. dimen.: H 835 (820 w/o lid), W 300, D 600 mm
- External dimensions: H 835 (820 w/o lid), W 300, D 600 mm

EAN: 4002515558102 / Material number: 10087320 / Old Material Number: 69859502D

Product category	
Fresh-water dishwashers	•
Tank dishwashers	•
Washer-disinfectors, laboratory	•
Thermal disinfectors	•
Washer-disinfectors, medical	•
Machine affiliation	
G 8066	•
PG 8067	•
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8063	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
PG 8581	•
PG 8562	•
PG 8582	•
PG 8582 CD	•
PG 8504	•
PG 8583	•
PG 8583 CD	•

PG 8595  
Aqua purificator  
for two full or partial demineralization cartridges.



EAN: 4002515558102 / Material number: 10087320 / Old Material Number: 69859502D

PG 8591	•
PG 8592	•
PG 8593	•
<b>Product category</b>	
Water treatment	•
<b>Product characteristics</b>	
Material	Stainless steel
Color	Stainless Steel
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
<b>Dimensions and weight</b>	
External dimensions, net height in inches	32 7/8 (835)
External dimensions, net width in inches	11 13/16 (300)
External dimensions, net depth in inches	23 5/8 (600)
External dimensions, gross height in inches	35 7/16 (900)
External dimensions, gross width in inches	15 3/4 (400)
External dimensions, gross depth in inches	29 3/16 (740)
Net weight in lbs	59 (26.50)
Gross weight in lbs	67 (30.00)