

UBS 2

Conversion kit

for use with selected series G 78 mobile units in PG 85 machines.



- For older injector units without drying unit connection

EAN: 4002515588987 / Material number: 10131100 / Old Material Number: 69215015D

Product category	
Washer-disinfectors, laboratory	•
Machine affiliation	
PG 8583	•
PG 8593	•
Product category	
Conversion kit	•
Product characteristics	
Material	Stainless steel, Plastic
Color	Stainless Steel, Black
Standard electrical connection	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
Dimensions and weight	
External dimensions, net height in inches	3 9/16 (90)
External dimensions, net width in inches	5 1/8 (129)
External dimensions, net depth in inches	11 5/8 (295)
External dimensions, gross height in inches	4 15/16 (125)
External dimensions, gross width in inches	6 1/2 (165)
External dimensions, gross depth in inches	13 13/16 (350)
Net weight in lbs	2 (0.51)
Gross weight in lbs	2 (0.71)