

KFNF 9955 iDE

FrenchDoor Bottom-mount Units

maximum convenience thanks to generous large capacity and ice maker.



- Food stays fresh for longer – PerfectFresh
- Optimum and maintenance-free LED lighting in compartment
- Door shelves can be cleaned in the dishwasher – ComfortClean
- No icing up of food and no need to defrost thanks to Frost free
- Ice cubes thanks to the plumbed IceMaker

EAN: 4002515655498 / Material number: 10277970 /
Old Material Number: 38995500USA

General information	
Model number	KFNF 9955 iDE
Manufacturer material number	10277970
EAN number	4002515655498
Marketing class	Platinum
Appliance category	
Fridge-freezer	•
Design	
Built-in	•
Built-in integrated	•
Door hinge side	Left and right
Design	
Type of lighting	LED
Freezer compartment lighting	LED
User convenience	
Freshness system	PerfectFresh
DynaCool	•
NoFrost	•
DuplexCool	•
VarioRoom	•
SoftClose door closing damper	•
IceMaker with plumbed water connection	•
Ice/Water dispenser with plumbed water connection	No
Control	
Electronic temperature display and control	TouchControl
Fridge compartment can be switched off	•
Independent temperature control of fridge and freezer compartments	•
SuperCool	•
SuperFrost	•
No. of temperature zones	3
Sabbath mode	•
Fridge/fridge zone	
No. of shelves	4
No. of humidity-controlled compartments	2
Number of door racks for cans	4
Door rack for bottles	2
Freezer/freezer zone	
Number of freezer drawers	2
Efficiency	
Energy Star Qualified	•
Safety	
Lock function	•
Acoustic door alarm	•
Acoustic temperature alarm, freezer section	•
Optical temperature alarm	•
Power cut indication for freezer compartment	•

KFNF 9955 iDE

FrenchDoor Bottom-mount Units

maximum convenience thanks to generous large capacity and ice maker.



EAN: 4002515655498 / Material number: 10277970 /

Old Material Number: 38995500USA

Technical data	
Niche width in inches (mm), min.	36 1/8 (915)
Niche width in inches (mm), max.	36 1/8 (915)
Niche height in inches (mm), min.	80 (2032)
Niche height in inches (mm), max.	81 5/8 (2072)
Niche depth in in.(mm)	24 5/8 (625)
Appliance width in in.(mm)	35 7/8 (910)
Appliance height in in.(mm)	79 3/4 (2027)
Appliance depth in in.(mm)	24 (610)
Weight in lbs.(kg)	358 (162.0)
Type of mounting	Fixed door
Fridge compartment volume in cu. ft. (l)	10.45 (296)
including PerfectFresh zone in l	2.44 (69)
4-star freezer compartment volume in cu. ft. (l)	6 (170)
Total usable capacity in cu. ft. (l)	18.89 (535)
Storage time in case of fault in h	40
Sound emissions in dB(A) re 1 pW	44
Current consumption in milliampere (mA)	2500
Voltage in V	115
Fuse rating in A	10
Number of phases	1
Frequency in Hz	60
Wire length in ft (m)	9 (2.8)
Replacing bulbs	Customer Service
Standard accessories	
Egg rack	•