

## PWT 6089 Vario [EL LP]

### Washer-dryer stack

for washing and drying in the smallest space, model with drain pump



- Drum volume 2.83 (80) ft<sup>3</sup> (l) l and/ or 6.36 (180.00) ft<sup>3</sup> (l) l, load size 2 x 18 (8.0) lb (kg) kg
- Large variety of Program – application specific Program
- Easy handling – centered control unit
- High laundry throughput – very short program cycles
- Gentle laundry care thanks to the Miele honeycomb drum

EAN: / Material number: 10411980 / Old Material Number:

<b>Construction type and design</b>	
Design	Front-loading stack
Linie	Professional
Front	Octo Blue
Washing machine load capacity in kg and p	18 (8.0) lb (kg)
Tumble dryer load capacity in kg and p	18 (8.0) lb (kg)
Washing machine fill ratio	1:10
Tumble dryer fill ratio	1:22,5
Washing machine drum volume in l and gal	2.83 (80) ft <sup>3</sup> (l)
Tumble dryer drum volume in l and gal	6.36 (180.00) ft <sup>3</sup> (l)
Drying system	Exhaust air
Washing machine door opening [dia.] in mm and in	14 5/8 (370) in (mm)
Tumble dryer door opening [dia.] in mm and in	17 5/16 (440) in (mm)
Door opening angle in degrees	180
Door hinge	Washing right/drying left
Maintenance-free motor with frequency converter in the washing machine	•
Honeycomb drum	•
<b>Application</b>	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for laundrettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for fire brigades and rescue services	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for domestic use	•
Suitable for doctors' and dentists' practices	•
<b>Performance data</b>	
Specific water consumption in l/kg and gal/p	8.25
Specific washing machine energy consumption in kWh/kg/p	0.06
Specific tumble dryer energy consumption in kWh/kg/p	0.95
Maximum tumble dryer evaporation capacity in l/hour and gal/hour	8 (8.1) gal (US)/min (l)
Washing machine program duration in min.	53
Tumble dryer program duration in min.	37
Residual moisture with cold rinse in %	49
Residual moisture with hot rinse in %	44
Washer-extractor spin speed in rpm.	1300
Washing machine g-factor	520
<b>Control</b>	
Control system	Profitronic L Vario
Programmability	programmable

PWT 6089 Vario [EL LP]

Washer-dryer stack

for washing and drying in the smallest space, model with drain pump



EAN: / Material number: 10411980 / Old Material Number:

Tumble dryer programme controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
<b>Standard/target group programs</b>	
Basic programmes	•
Programmes for the hotel and catering industry	•
Programmes for retirement and care homes	•
Programmes for laundrettes	•
Programmes for residential homes and apartments	•
Programmes for dry cleaners	•
Programmes for commercial laundries	•
Programmes for small businesses	•
Programmes for fire brigades and rescue services	•
Programmes for universities, nurseries, and school	•
Programmes for hospitals	•
Programmes for camp sites	•
Programmes for sports clubs	•
Programmes for beauty clinics, spas, and fitness studios	•
Programmes for domestic use	•
Programmes for doctors' and dentists' practices	•
<b>Washing machine dispensing</b>	
Detergent dispenser drawer	3 compartments
Patented liquid dispensing adapter	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•
<b>Standard electrical connection</b>	
Type of heating washing machine	Electric
Type of heating tumble dryer	Electric
Electrical connection washing machine	3 AC 208 V 60 Hz
Heater rating washing machine in kW	6.50
Total connected load washing machine in kW	6.75
Fuse rating washing machine in A	30.0
Electrical connection tumble dryer	3 AC 208 V 60 Hz
Heater rating tumble dryer in kW	7.64
Total connected load tumble dryer in kW	8.20
Fuse rating tumble dryer in A	30.0
<b>Possible voltage variants</b>	
Electrical connection washing machine	3 AC 208 V 60 Hz
Heater rating washing machine in kW	7.64
Total connected load washing machine in kW	8.20
Fuse rating washing machine in A	30.0
<b>Water connection/drainage</b>	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Grey water (optional) [number]	1 x 1/2" w/ 3/4" union
Drain pump	DN 22

PWT 6089 Vario [EL LP]

Washer-dryer stack

for washing and drying in the smallest space, model with drain pump