

DA 6996 W Pearl

Wall ventilation hood

with dimmable ambient lighting for a unique lighting mood in your kitchen.



- Design highlight – 35 1/2 (900) in (mm) wide bowed glass canopy
- Unique convenience – Con@ctivity 2.0
- Energy-efficient and uniform lighting – LED light strip
- Energy-efficient and quiet

EAN: 4002515780381 / Material number: 10418850 /  
Old Material Number: 28699630USA

<b>Construction type and design</b>	
Appliance colour	Brilliant white
<b>Design</b>	
Wall ventilation hood	•
<b>Operating modes</b>	
Recirculated mode	Can be retrofitted
<b>Design</b>	
Edge extraction	•
<b>User convenience</b>	
Automatic function	Con@ctivity 2.0
Electronic controls	•
Operation	Light-touch sw.w.LEDs+r. contr.
Power levels (number excl. Intensive)	3
Booster levels	1
Programmable Intensive switch-off	•
Delayed shutdown for 5 or 15 minutes	•
Grease filter saturation indicator	•
Active charcoal filter saturation indicator	•
<b>Cleaning convenience</b>	
Easy-to-clean canopy interior – CleanCover	•
<b>Filter system</b>	
Number of dishwasher-safe stainless steel grease filters (10-ply)	1
<b>Lighting</b>	
LED	•
Number x W	1x9,7 W / 1x12,8 W
Light intensity in Lx	600 lx
Color temperature in K	3000 Kelvin
Light dimmer function	•
Ambient lighting white	•
<b>Blower</b>	
Dual-action blower	•
AC motor	•
<b>Exhaust air</b>	
Air throughput	Values upon request
<b>Safety</b>	
Safety shut-off	•
Single-ply safety glass (ESG)	•
<b>Technical data</b>	
Overall hood height for vented mode and external in inches (mm)	23 (583)
Overall height for recirculation mode ventilation hoods in mm	23 (583)
Overall min. height for vented and external in in. (mm)	23 (583)
Canopy width in in.(mm)	35 1/2 (900)
Overall max. height for vented and external in in. (mm)	23 (583)
Canopy height in in.(mm)	23 (583)
Overall min. height for recirculation in in. (mm)	23 (583)

DA 6996 W Pearl

Wall ventilation hood

with dimmable ambient lighting for a unique lighting mood in your kitchen.




EAN: 4002515780381 / Material number: 10418850 /  
Old Material Number: 28699630USA

Canopy depth in in.(mm)	21 1/4 (537)
Overall max. height for recirculation in in. (mm)	23 (583)
Net weight in lbs. (kg)	62 (28.0)
Length of electrical wire in ft (m)	4 (1.5)
Standard plug fitted	•
Hard-wired	•
Number of phases	1
Total connected load in kW	0.37
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
<b>Installation note</b>	
Vent connection at top	•
Vent connection at top and rear	•
Diameter of vent connection in in.(mm)	6 (150)
<b>Standard accessories</b>	
Reducer from 150 to 125 mm Ø	•
Communication module for Con@ctivity XKM 2000 DA	XKS 3000 Z
Non-return flap	•
<b>Optional accessories</b>	
OdorFree charcoal filter, can be reactivated	DKF 25-R
Duct Cover	DADC 6000

## DA 6996 W Pearl

### Wall ventilation hood

with dimmable ambient lighting for a unique lighting mood in your kitchen.



#### DA 6998 W (Installation drawing) – USA

1) Cut-out for cooker hoods with hard-wired connection rather than a plug, 2) Opening for ducting connection at the back. Vent Connection alternatively to the top, 3) Ventilation grille positioned at the top for recirculation. A distance of at least 200 mm must be maintained between the top of the appliance and the ceiling or any furniture units installed above the appliance.