

## DA 1280

### 30-inch built-under ventilation hood

with energy-efficient LED lighting and sliding switch for simple operation.



- Puristic design – space-saving solution 30 (760) in (mm) wide
- Powerful – ?? in Booster level
- Efficient filtration- 10-ply stainless steel grease filters
- Safe and easy to clean – Miele CleanCover
- Suitable for every home – vented or recirculating


EAN: 4002515774403 / Material number: 10451490 /  
Old Material Number: 28128055USA

<b>Construction type and design</b>	
Color	Stainless steel
<b>Design</b>	
Built-under ventilation hood	•
<b>Operating modes</b>	
Recirculated mode	Can be retrofitted
OdorFree charcoal filter (order separately)	DKF 18-900
<b>User convenience</b>	
Recessed knob controls	•
Power levels (number excl. Intensive)	3
Slide switch	•
Booster levels	1
<b>Cleaning convenience</b>	
Easy-to-clean CleanCover hood liner	•
<b>Filter system</b>	
Number of dishwasher-safe stainless-steel grease filters	3
<b>Lighting</b>	
LED	•
Number x W	2 x 3 W
Light intensity in lx	275 lx
Color temperature in K	3000 Kelvin
<b>Blower</b>	
Single-action blower	•
AC motor	•
<b>Exhaust air</b>	
Maximum air throughput in cfm according to HVI	220
Air throughput	Values upon request
<b>Technical data</b>	
Canopy width in in.(mm)	30 (760)
Canopy height in in.(mm)	5 (125)
Canopy depth in in.(mm)	19 3/4 (500)
Net weight in lbs. (kg)	29 (12.9)
Length of electrical wire in ft (m)	4 (1.5)
Standard plug fitted	•
Number of phases	1
Total connected load in kW	0.28
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
<b>Installation note</b>	
Vent connection at top	•
Diameter of vent connection in in.(mm)	6 (150)
Installation template	•
<b>Standard accessories</b>	
Recirculation deflector	•
Non-return flap	•

DA 1280

30-inch built-under ventilation hood

with energy-efficient LED lighting and sliding switch for simple operation.



DA 1180, Stainless steel (installation drawing)