

WWH860 WCS TDos&IntenseWash WiFi

W1 front-loading washing machine:

With TwinDos & IntenseWash for revolutionary Miele cleanliness & convenience.



- There's no faster way to wash – QuickIntenseWash
- Precise and automatic detergent dispensing with TwinDos®
- Exclusive CapDosing range for different fabrics and stains
- The SoftSteam extra reduces creasing and saves up to 50% time and effort
- ENERGY STAR® qualified

EAN: 4002515830468 / Material number: 10666200 / Old Material Number: 11WH8605USA

Design	
Stackable	•
Side-by-side	•
Slot-in	•
Door hinging	left
Type	
Product brand	W1 White Edition
Front loaders	•
Spinning	
Max. spin speed	1600
Rinse hold	•
Without spin" function	•
Design	
Appliance color	Lotus white
Fascia color	Lotus white
Door design	Lotus white with chrome ring
Rotary selector color	Lotus White / Chrome ring
Fascia panel version	5° inclined
Control type	Selector dial
Control panel	ComfortSensor white, 1 line
Cleaning performance	
Innovative IntenseWash technology	•
TwinDos automatic dispensing of detergent	•
CapDosing portioned dispensing	•
Gentle laundry care	
Honeycomb drum	•
Load in lbs. (kg)	18 (8.0)
User convenience	
Networking with Miele@home	•
Delay start up to 24 hours	•
Countdown indicator	•
Programme sequence indicator	•
Drum lighting	LED
MultiLingua	•
AutoClean dispenser drawer	•
Efficiency and sustainability	
Hot water connection	•
EcoFeedback	•
Low-temperature washing "Cold" and "68°F"	•
Automatic load control	•
Flow meter	•
Foam control	•
ProfiEco motor	•
Wash programs	
Delicates	•
Express	•
Outdoor	•
Proofing	•
Normal	•

WWH860 WCS TDos&IntenseWash WiFi

W1 front-loading washing machine:

With TwinDos & IntenseWash for revolutionary Miele cleanliness & convenience.



EAN: 4002515830468 / Material number: 10666200 / Old Material Number: 11WH8605USA

Wrinkle-free	•
Sanitize	•
Handwash	•
Dress shirts	•
Extra White	•
Darks/Denims	•
QuickIntenseWash	•
Table Linens/Drapes	•
Sportswear	•
Woolens	•
Silks	•
Drain/Spin	•
QuickRinse	•
Baby Clothes	•
Towels	•
Downs	•
Pillows	•
Care – Clean Machine	•
Care – Clean TwinDos	•
Settings – Anti-Crease	•
Washing extras	
SingleWash	•
Soak	•
Pre-rinse	•
SoftSteam with steam	•
Choosing the degree of soiling	•
Quality	
Counterweights made of cast iron	•
Safety	
Water protection system	Watercontrol-System
Child lock	•
Lock code	•
Optical interface	•
Technical data	
Dimensions (width) in in. (mm)	23 1/2 (596)
Dimensions (height) in in. (mm)	33 1/2 (850)
Dimensions (depth) in in. (mm)	25 3/8 (643)
Depth with door open in in. (mm)	42 1/2 (1077)
Weight in lbs. (kg)	212 (96)
Total connected load in kW	1.30
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
Length of supply lead in ft. (m)	6 (2)
Standard accessories	
3 capsules	•
UltraPhase 1+2	•