

## PUR 88 W

### 30-inch wall-mounted ventilation hood

with energy-efficient LED lighting and backlit controls for easy use.



- Timeless design – stainless steel canopy 29 1/2 (748) in (mm) wide
- Powerful – ?? in Booster level
- Efficient filtration- 10-ply stainless steel grease filters
- Safe and easy to clean – Miele CleanCover
- Suitable for every home – vented or recirculating

EAN: 4002515941638 / Material number: 10743170 /  
Old Material Number: 28428654USA

<b>Construction type and design</b>	
Color	Stainless steel
<b>Design</b>	
Wall ventilation hood	•
<b>Operating modes</b>	
Recirculated mode	Can be retrofitted
Recirculation conversion kit (order separately)	DUW 20
OdorFree charcoal filter (order separately)	DKF 12-900
<b>User convenience</b>	
Electronic controls	•
Power levels (number excl. Intensive)	3
Operation	Light-touch switches with LEDs
Booster levels	1
Programmable Intensive switch-off	•
<b>Cleaning convenience</b>	
Easy-to-clean CleanCover hood liner	•
<b>Filter system</b>	
Number of dishwasher-safe stainless-steel grease filters	2
<b>Lighting</b>	
LED	•
Number x W	2 x 3 W
Light intensity in Lx	330 lx
Color temperature in K	3000 Kelvin
<b>Blower</b>	
Dual-action blower	•
AC motor	•
<b>Exhaust air</b>	
Maximum air throughput in cfm according to HVI	418
Air throughput	Values upon request
<b>Safety</b>	
Safety shut-off	•
<b>Technical data</b>	
Overall hood height for vented mode and external in inches (mm)	27 (685)–39 5/8 (1005)
Overall hood height for recirculation and external in inches (mm)	32 1/8 (815)–44 3/4 (1135)
Overall min. height for vented and external in in. (mm)	27 (685)
Canopy width in in.(mm)	29 1/2 (748)
Overall max. height for vented and external in in. (mm)	39 5/8 (1005)
Canopy height in in.(mm)	2 1/2 (62)
Overall min. height for recirculation in in. (mm)	32 1/8 (815)
Canopy depth in in.(mm)	19 3/4 (500)
Overall max. height for recirculation in in. (mm)	44 3/4 (1135)
Net weight in lbs. (kg)	51 (23.0)
Length of electrical wire in ft (m)	4 (1.5)
Standard plug fitted	•
Minimum distance above electric cooktops in in. (mm)	24 1/8 (610)

## PUR 88 W

30-inch wall-mounted ventilation hood

with energy-efficient LED lighting and backlit controls for easy use.



EAN: 4002515941638 / Material number: 10743170 /

Old Material Number: 28428654USA

Minimum height above gas cooktop (max. 12.6 kW total power, burner  $\leq$  4.5 kW) in mm

26 (660)

Number of phases

1

Total connected load in kW

0.35

Voltage in V

120

Fuse rating in A

15

Frequency in Hz

60

### Installation note

Vent connection at top

•

Vent connection at top and rear

•

Diameter of vent connection in in.(mm)

6 (150)

Telescopic chimney

•

### Standard accessories

Reducer from 150 to 125 mm  $\varnothing$

•


Non-return flap

•

## PUR 88 W

30-inch wall-mounted ventilation hood

with energy-efficient LED lighting and backlit controls for easy use.



PUR88W, DAP1727 (Installation drawing) – USA/CDN

1) Extraction, 2) Recirculation, 3) Ventilation grille at top for recirculation, 4+5) Installation cut-out (5 not required for recirculation)