

F 2811 Vi

MasterCool™ freezer

For high-end design and technology on a large scale.



- Push2open for convenient door-opening assistance
- Light floods the interior thanks to LED elements – BrilliantLight
- Fresh ice cubes from the IceMaker with plumbed water connection
- Communication with the machine could not be easier – WiFi Conn@ct
- Convenient control thanks to color touch display MasterSensor

EAN: 4002515901434 / Material number: 10744900 /

Old Material Number: 37281101USA

General information	
Model number	F 2811 Vi
Manufacturer material number	10744900
EAN number	4002515901434
Marketing class	Diamond
Appliance category	
Freezer	•
Design	
Built-in	•
Built-in integrated	•
Door hinge side	Left
Convertible hinging	•
Can be installed side-by-side	•
Design	
Lighting	BrilliantLight
User convenience	
Networking with Miele@home	•
Electronic temperature display and control	MasterSensor
Sabbath mode	•
NoFrost	•
SoftClose door closing damper	•
IceMaker with mains water connection	•
Push2open	•
FullAccess	•
EasyClean	•
MaxLoad hinge	•
Smart Extras	
Cooling tips	•
Cooling modes	•
IceMaker	•
Push notifications	•
RemoteUpdate	•
Smart Home Integration	•
Control	
SuperFrost	•
No. of temperature zones	1
Eco mode	•
Freezer/freezer zone	
Number of shelves	2
Number of freezer baskets	2
Door baskets – small	1
Door baskets – large	3
Efficiency	
Energy Star Qualified	•
Safety	
Lock function	•
Acoustic door alarm	•
Acoustic temperature alarm, freezer section	•

F 2811 Vi

MasterCool™ freezer

For high-end design and technology on a large scale.



EAN: 4002515901434 / Material number: 10744900 /

Old Material Number: 37281101USA

Optical door alarm	•
Optical temperature alarm	•


Technical data	
Niche width in inches (mm), min.	30 (762)
Niche width in inches (mm), max.	30 (762)
Niche height in inches (mm), min.	84 1/8 (2134)
Niche height in inches (mm), max.	84 1/8 (2134)
Niche depth in in.(mm)	24 7/8 (629)
Appliance width in in.(mm)	29 3/4 (756)
Appliance height in in.(mm)	83 3/4 (2127)
Appliance depth in in.(mm)	23 7/8 (608)
Weight in lbs.(kg)	351 (158.8)
Maximum fridge compartment door front weight in lbs. (kg)	62 (28)
4-star freezer compartment volume in cu. ft. (l)	15.75 (446)
Sound emissions in dB(A) re 1 pW	42
Current consumption in milliampere (mA)	4000
Voltage in V	120
Fuse rating in A	10
Number of phases	1
Frequency in Hz	60
Wire length in ft (m)	9 (3.0)
Replacing bulbs	Customer Service

Available display languages	
-----------------------------	--


Available display languages via MultiLingua

? ? ? ? ? ? ? , ?
 ? , ? ? ? ? ? , deutsch,
 dansk, english, english
 (AU), english (CA), english
 (GB), english (US), eesti,
 suomi, français, français
 (CA), français (FR),
 ελληνικά, italiano, ? ?
 ? , ? ? ? , hrvatski,
 latviesu, lietuviu, bahasa
 malaysia, nederlands, norsk,
 polski, português, română,
 русский, svenska, srpski,
 slovenčina, slovensčina,
 español, čeština, türkçe,
 українська, magyar

F 2811 Vi
MasterCool™ freezer
For high-end design and technology on a large scale.




laying of cabling and pipework, MasterCool (Sketch)




Side-by-side, MasterCool, without partition wall, with heating mat (Sketch) (with footnote)


1) Heating mat KSK 2001 (EU, AUS, CN) or KSK 2002 (US, CA, MX, BR)




F2812Vi, F2813Vi, F2802Vi, F2811Vi, F2801Vi, MasterCool, inner space, installation drawings



KFP3005ed/cs, KFP3004ed/cs, Front panel, Front dimensions, MasterCool II, installation drawings



Sideview, MasterCool, Sketch




Side-by-Side, MasterCool, footnote, installation drawings

1. KSK 2001/2002, 2. Device A, 3. Device B, A = niche device A, B = niche device B

F 2811 Vi


MasterCool™ freezer

For high-end design and technology on a large scale.



F2802Vi, F2812Vi, F2813Vi, F2812SF, F2801Vi, F2811Vi, F2811SF, installation, MasterCool, installation drawings

1. View from the front, 2. Mains Connection cable, L = 3000 mm (118 inch), 3. Water inlet position, L = 2000 mm (not for KON USA), 4. No water/ELT connections permitted in this area



Opening angle 90°/115°, right side stop, MasterCool (Sketch) with footnote

A) Appliance door, F 2411 Vi: 525 mm (20 2/3 inch), F 2412 Vi, F 2412 SF, F 2413Vi, F 2472 Vi, F 2472 SF: 525 mm (20 2/3 inch), F 2671 Vi: 677 mm (26 2/3 inch), F 2672 Vi, F 2672 SF: 677 mm (26 2/3 inch), F 2812 SF, F 2812 Vi, F 2813 Vi: 829 mm (32 2/3 inch), F 2912 Vi, F 2912 SF: 982 mm (38 2/3 inch), B) Furniture front (max. 38 mm) (1 1/2 inch), C) Door handle, D) Distance from the door to the wall (without furniture front and door handle): F 2411 Vi: 237 mm (9 1/3 inch), F 2412 Vi, F 2412 SF, F 2472 Vi, F 2472 SF: 237 mm (9 1/3 inch), F 2672 Vi, F 2672 SF: 296 mm (11 2/3 inch), F 2811 Vi: 363 mm (14 1/3 inch), F 2812 SF, F 2812 Vi: 363 mm (14 1/3 inch), F 2912 Vi, F 2912 SF: 428 mm (16 7/8 inch), E) ONLY valid for SF versions: A + 25 mm (1 inch)