

F 2461 Vi

MasterCool™ freezer

Integrated IceMaker features separate water and ice dispensers.



- Push2open for convenient door-opening assistance
- Light floods the interior thanks to LED elements – BrilliantLight
- Ice and cooled-water dispensers for maximum convenience
- Communication with the machine could not be easier – WiFi Conn@ct
- Convenient control thanks to color touch display MasterSensor

EAN: 4002515901496 / Material number: 10745050 /

Old Material Number: 37246101USA

General information	
Model number	F 2461 Vi
Manufacturer material number	10745050
EAN number	4002515901496
Marketing class	Diamond
Appliance category	
Freezer	•
Design	
Built-in	•
Built-in integrated	•
Door hinge side	right
Can be installed side-by-side	•
Design	
Lighting	BrilliantLight
User convenience	
Networking with Miele@home	•
Electronic temperature display and control	MasterSensor
Sabbath mode	•
NoFrost	•
SoftClose door closing damper	•
Ice/Water dispenser with plumbed water connection	•
Push2open	•
FullAccess	•
EasyClean	•
MaxLoad hinge	•
Smart Extras	
Cooling tips	•
Cooling modes	•
Push notifications	•
RemoteUpdate	•
Smart Home Integration	•
Control	
SuperFrost	•
No. of temperature zones	1
Eco mode	•
Freezer/freezer zone	
Number of shelves	2
Number of freezer baskets	2
Door baskets – small	1
Door baskets – large	3
Safety	
Lock function	•
Acoustic door alarm	•
Acoustic temperature alarm, freezer section	•
Optical door alarm	•
Optical temperature alarm	•
Technical data	
Niche width in inches (mm), min.	18 (457)

F 2461 Vi MasterCool™ freezer

Integrated IceMaker features separate water and ice dispensers.



EAN: 4002515901496 / Material number: 10745050 /
Old Material Number: 37246101USA

Niche width in inches (mm), max.	18 (457)
Niche height in inches (mm), min.	84 1/8 (2134)
Niche height in inches (mm), max.	84 1/8 (2134)
Niche depth in in.(mm)	24 7/8 (629)
Appliance width in in.(mm)	17 3/4 (451)
Appliance height in in.(mm)	83 3/4 (2127)
Appliance depth in in.(mm)	23 7/8 (608)
Weight in lbs.(kg)	293 (132.7)
Maximum fridge compartment door front weight in lbs. (kg)	157 (71)
4-star freezer compartment volume in cu. ft. (l)	7.73 (219)
Sound emissions in dB(A) re 1 pW	42
Current consumption in milliampere (mA)	4000
Voltage in V	120
Fuse rating in A	10
Number of phases	1
Frequency in Hz	60
Wire length in ft (m)	9 (3.0)
Replacing bulbs	Customer Service

Available display languages




Available display languages via MultiLingua

? ? ? ? ? ? ? , ?
 ? , ? ? ? ? ? , deutsch,
 dansk, english, english
 (AU), english (CA), english
 (GB), english (US), eesti,
 suomi, français, français
 (CA), français (FR),
 ελληνικά, italiano, ? ?
 ? , ? ? ? ? , hrvatski,
 latviesu, lietuvii, bahasa
 malaysia, nederlands, norsk,
 polski, português, română,
 русский, svenska, srpski,
 slovenčina, slovenščina,
 español, čeština, türkçe,
 українська, magyar

F 2461 Vi

MasterCool™ freezer

Integrated IceMaker features separate water and ice dispensers.






18 inch, connection for power/water supply, Master Cool (US, CA, MX) (Sketch)

Side-by-side, MasterCool, without partition wall, with heating mat (Sketch) (with footnote)

F2462Vi, F2472Vi, F2461Vi, F2471Vi, MasterCool, installation, installation drawings (US, CA)

1) Heating mat KSK 2001 (EU, AUS, CN) or KSK 2002 (US, CA, MX, BR)




Sideview, MasterCool, Sketch

Side-by-Side, MasterCool, footnote, installation drawings

KFP1845ed/cs, KFP1844ed/cs, MasterCool, Front panel, Front dimensions, sketch (US, CA)

1. KSK 2001/2002, 2. Device A, 3. Device B, A = niche device A, B = niche device B



F2413Vi, F2471Vi, F2471SF, F2461Vi, F2411Vi, F2411SF, installation, MasterCool, installation drawings

1. View from the front, 2. Mains Connection cable, L = 3000 mm (118 inch), 3. Water inlet position, L = 2000 mm (not for KON USA), 4. No water/ELT connections permitted in this area