

F 2471 Vi

MasterCool™ freezer

For high-end design and technology on a large scale.



- Push2open for convenient door-opening assistance
- Light floods the interior thanks to LED elements – BrilliantLight
- Ice and cooled-water dispensers for maximum convenience
- Communication with the machine could not be easier – WiFi Conn@ct
- Convenient control thanks to color touch display MasterSensor

EAN: 4002515901519 / Material number: 10745080 /  
Old Material Number: 37247101USA

| General information                               |                |
|---------------------------------------------------|----------------|
| Model number                                      | F 2471 Vi      |
| Manufacturer material number                      | 10745080       |
| EAN number                                        | 4002515901519  |
| Marketing class                                   | Diamond        |
| Appliance category                                |                |
| Freezer                                           | •              |
| Design                                            |                |
| Built-in                                          | •              |
| Built-in integrated                               | •              |
| Door hinge side                                   | Left           |
| Can be installed side-by-side                     | •              |
| Design                                            |                |
| Lighting                                          | BrilliantLight |
| User convenience                                  |                |
| Networking with Miele@home                        | •              |
| Electronic temperature display and control        | MasterSensor   |
| Sabbath mode                                      | •              |
| NoFrost                                           | •              |
| SoftClose door closing damper                     | •              |
| Ice/Water dispenser with plumbed water connection | •              |
| Push2open                                         | •              |
| FullAccess                                        | •              |
| EasyClean                                         | •              |
| MaxLoad hinge                                     | •              |
| Smart Extras                                      |                |
| Cooling tips                                      | •              |
| Cooling modes                                     | •              |
| Push notifications                                | •              |
| RemoteUpdate                                      | •              |
| Smart Home Integration                            | •              |
| Control                                           |                |
| SuperFrost                                        | •              |
| No. of temperature zones                          | 1              |
| Eco mode                                          | •              |
| Freezer/freezer zone                              |                |
| Number of shelves                                 | 2              |
| Number of freezer baskets                         | 2              |
| Door baskets – small                              | 1              |
| Door baskets – large                              | 3              |
| Efficiency                                        |                |
| Energy Star Qualified                             | •              |
| Safety                                            |                |
| Lock function                                     | •              |
| Acoustic door alarm                               | •              |
| Acoustic temperature alarm, freezer section       | •              |
| Optical door alarm                                | •              |
| Optical temperature alarm                         | •              |

F 2471 Vi

MasterCool™ freezer

For high-end design and technology on a large scale.



EAN: 4002515901519 / Material number: 10745080 /  
Old Material Number: 37247101USA

#### Technical data

|                                                           |                  |
|-----------------------------------------------------------|------------------|
| Niche width in inches (mm), min.                          | 18 (457)         |
| Niche width in inches (mm), max.                          | 18 (457)         |
| Niche height in inches (mm), min.                         | 84 1/8 (2134)    |
| Niche height in inches (mm), max.                         | 84 1/8 (2134)    |
| Niche depth in in.(mm)                                    | 24 7/8 (629)     |
| Appliance width in in.(mm)                                | 17 3/4 (451)     |
| Appliance height in in.(mm)                               | 83 3/4 (2127)    |
| Appliance depth in in.(mm)                                | 23 7/8 (608)     |
| Weight in lbs.(kg)                                        | 293 (132.7)      |
| Maximum fridge compartment door front weight in lbs. (kg) | 157 (71)         |
| 4-star freezer compartment volume in cu. ft. (l)          | 7.73 (219)       |
| Sound emissions in dB(A) re 1 pW                          | 42               |
| Current consumption in milliampere (mA)                   | 4000             |
| Voltage in V                                              | 120              |
| Fuse rating in A                                          | 10               |
| Number of phases                                          | 1                |
| Frequency in Hz                                           | 60               |
| Wire length in ft (m)                                     | 9 (3.0)          |
| Replacing bulbs                                           | Customer Service |

#### Available display languages


Available display languages via MultiLingua

? ? ? ? ? ? ? , ?  
 ? , ? ? ? ? ? , deutsch,  
 dansk, english, english  
 (AU), english (CA), english  
 (GB), english (US), eesti,  
 suomi, français, français  
 (CA), français (FR),  
 ελληνικά, italiano, ? ?  
 ? , ? ? ? ? , hrvatski,  
 latviesu, lietuviu, bahasa  
 malaysia, nederlands, norsk,  
 polski, português, română,  
 русский, svenska, srpski,  
 slovenčina, slovenščina,  
 español, čeština, türkçe,  
 українська, magyar


F 2471 Vi

MasterCool™ freezer

For high-end design and technology on a large scale.




18 inch, connection for power/water supply, MasterCool (US, CA, MX) (Sketch)




Side-by-side, MasterCool, without partition wall, with heating mat (Sketch) (with footnote)


1) Heating mat KSK 2001 (EU, AUS, CN) or KSK 2002 (US, CA, MX, BR)



F2462Vi, F2472Vi, F2461Vi, F2471Vi, MasterCool, installation, installation drawings (US, CA)




Sideview, MasterCool, Sketch




Side-by-Side, MasterCool, footnote, installation drawings

1. KSK 2001/2002, 2. Device A, 3. Device B, A = niche device A, B = niche device B



KFP1845ed/cs, KFP1844ed/cs, MasterCool, Front panel, Front dimensions, sketch (US, CA)



F2413Vi, F2471Vi, F2471SF, F2461Vi, F2411Vi, F2411SF, installation, MasterCool, installation drawings

1. View from the front, 2. Mains Connection cable, L = 3000 mm (118 inch), 3. Water inlet position, L = 2000 mm (not for KON USA), 4. No water/ELT connections permitted in this area