

Complete C3 Calima PowerLine - SGFE0  
canister vacuum cleaners  
with HEPA filter for the greatest Filtration demands.



- High suction power – 1200 W
- Reliably removes pet hair and lint with turbo brush.
- Gentle on delicate hard floors – flexible Parquet Twister
- Maximum air hygiene with HEPA filter: 'Ideal for allergy sufferers
- No need to stoop thanks to plus/minus foot controls

\* According to EN 60312-1

EAN: 4002515949580 / Material number: 10796510 / Old Material Number: 41GFE040USA

Design	
Canister vacuum cleaner with dustbag	•
Product line	Complete C3
Motor type	PowerLine
Product type	SGFE0
Appliance color	Curry yellow
User convenience	
Electronic suction power setting	+/- footswitches
Illuminated power indicator	•
Electrobrush socket	•
Ergonomic carrying handle	•
Ergonomic handle	•
Silence system	•
Telescopic suction wand	Comfort telescopic wand
Park system for vacuuming breaks	•
Park system for storage	on both sides
One-touch automatic cord rewind	•
Efficiency and sustainability	
Nominal power consumption in W	1100
Mobility	
Caster wheels gentle on floors	•
Three-point maneuverability	•
Operating radius in ft (m)	36 (11)
Cord length in ft (m)	24 (7.5)
Filter system	
FilterBag type	HyClean GN
FilterBag™ volume in qt (US) (l)	4.8 (4.5) qt (US) (l)
FilterBag™ change indicator	•
Exhaust filter	HEPA AirClean filter
Motor protection filter	•
Safety	
Locking system for floorhead and handle	•
Automatic FilterBag™ positioning	•
All-round bumper strip	•
Technical data	
Power	1200
Width in inches (mm)	19 5/8 (496)
Height in inch (mm)	227
Weight in lbs (kg)	20 (8.8)
Standard accessories	
Three-piece accessory set	Integrated
Upholstery nozzle	•
Crevice nozzle	•
Dusting brush with synthetic bristles	•
Floorbrush	SBB 300-3 Parquet Twister
Parquet Twister Floorhead SBB 300-3	•
Turbobrush	STB 305-3
Turbo Brush Floorhead STB 305-3	•
Filter	HEPA AirClean filter
Cleaning brush	No