

Compact C1 HomeCare PowerLine - SCAO3
canister vacuum cleaners
with turbo brush for hard floor and low, medium-pile carpeting.



- High suction power – 1200 W
- Reliably removes pet hair and lint with turbo brush.
- Adjustable working height – Stainless steel telescopic tube
- Effortless vacuuming of large areas w/ 29.5 ft operating radius

EAN: 4002515977699 / Material number: 10850050 / Old Material Number: 41CAE036USA

Design	
Canister vacuum cleaner with dustbag	•
Product line	Compact C1
Motor type	PowerLine
Product type	SCAE0
Appliance color	Autumn red
User convenience	
Electronic suction power setting	6-stage rotary selector
Ergonomic carrying handle	•
Ergonomic handle	•
Telescopic suction wand	Stainless steel telescopic wand
Park system for vacuuming breaks	•
Park system for storage	on one side
Efficiency and sustainability	
Nominal power consumption in W	1100
Mobility	
Caster wheels gentle on floors	•
Three-point maneuverability	•
Operating radius in ft (m)	9.0
Filter system	
FilterBag type	HyClean FJM
FilterBag™ volume in qt (US) (l)	3.5
FilterBag™ change indicator	•
Exhaust filter	AirClean filter
Motor protection filter	•
Safety	
Locking system for floorhead and handle	•
Automatic FilterBag™ positioning	•
Technical data	
Power	1200
Height in inch (mm)	230
Weight in lbs (kg)	6.70
Standard accessories	
Three-piece accessory set	On VarioClip
Upholstery nozzle	•
Crevice nozzle	•
Dusting brush with synthetic bristles	•
SBD 365-3 floorhead	•
Turbobrush	STB 305-3
Turbo Brush Floorhead STB 305-3	•
Filter	AirClean filter
Cleaning brush	No