

DA 2588

Insert ventilation hood
with energy-efficient LED lighting and backlit controls for easy use.



- Customized kitchen design – fully integrated in 31 5/8 (802) in (mm) width
- Unique user convenience – Con@ctivity
- Powerful – 500.29 (850) ft³/min (m³/h) in Booster level
- Efficient filtration- 10-ply stainless steel grease filters
- Safe and easy to clean – Miele CleanCover

EAN: 4002516024705 / Material number: 10876770 /
Old Material Number: 28258855USA

Construction type and design	
Color	Stainless steel
Design	
Insert ventilation hood	•
Operating modes	
Recirculated mode	Can be retrofitted
Recirculation conversion kit (order separately)	DUU 151
OdorFree charcoal filter (order separately)	DKF 15-900
User convenience	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number excl. Intensive)	3
Booster levels	1
Programmable Intensive switch-off	•
Delayed shutdown for 5 or 15 minutes	•
Grease filter saturation indicator	•
Active charcoal filter saturation indicator	•
Cleaning convenience	
Easy-to-clean CleanCover hood liner	•
Filter system	
Number of dishwasher-safe stainless-steel grease filters	2
Lighting	
LED	•
Number x W	2 x 3 W
Light intensity in lx	300 lx
Color temperature in K	3000 Kelvin
Blower	
Dual-action blower	•
AC motor	•
Exhaust air	
Maximum air throughput in cfm according to HVI	415
Air throughput	Values upon request
Air throughput in booster level 1 (cfm) (m ³ /h)	500.29 (850)
Safety	
Safety shut-off	•
Technical data	
Canopy width in in.(mm)	31 5/8 (802)
Canopy height in in.(mm)	2 (50)
Canopy depth in in.(mm)	15 7/8 (402)
Net weight in lbs. (kg)	27 (12.1)
Length of electrical wire in ft (m)	2 (0.8)
Standard plug fitted	•
Minimum distance above electric cooktops in in. (mm)	24 1/8 (610)
Minimum height above gas cooktop (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	26 (660)
Number of phases	1
Total connected load in kW	0.35

DA 2588

Insert ventilation hood

with energy-efficient LED lighting and backlit controls for easy use.



EAN: 4002516024705 / Material number: 10876770 /
Old Material Number: 28258855USA

Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60

Installation note

Vent connection at top	•
Diameter of vent connection in in.(mm)	6 (150)

Standard accessories

Communication module for Con@ctivity XKM 2000 DA	XKS 3000 Z
Non-return flap	•