

DA 2698

Insert ventilation hood
with energy-efficient LED lighting and backlit controls for easy use.



- Customized kitchen design – fully integrated in 34 3/4 (880) in (mm) width
- Unique user convenience – Con@ctivity
- Powerful – ?? in Booster level
- Energy-efficient and quiet
- Elegant and efficient – edge vented panel

EAN: 4002516023906 / Material number: 10876810 /
Old Material Number: 28269855USA

Construction type and design	
Color	Stainless steel
Design	
Insert ventilation hood	•
Operating modes	
Recirculated mode	Can be retrofitted
Recirculation conversion kit (order separately)	DUU 151
OdorFree charcoal filter (order separately)	DKF 19-P
Design	
Edge extraction	•
User convenience	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number excl. Intensive)	3
Booster levels	1
Programmable Intensive switch-off	•
Delayed shutdown for 5 or 15 minutes	•
Grease filter saturation indicator	•
Active charcoal filter saturation indicator	•
Efficiency and sustainability	
ECO motor	•
PowerManagement system	•
Cleaning convenience	
Easy-to-clean CleanCover hood liner	•
Filter system	
Number of dishwasher-safe stainless-steel grease filters	2
Lighting	
LED	•
Number x W	4 x 3 W
Light intensity in Lx	650 lx
Color temperature in K	3500 Kelvin
Light dimmer function	•
Blower	
Dual-action blower	•
DC motor	•
Exhaust air	
Maximum air throughput in cfm according to HVI	401
Air throughput	Values upon request
Safety	
Safety shut-off	•
Technical data	
Canopy width in in.(mm)	34 3/4 (880)
Canopy height in in.(mm)	2 1/2 (63)
Canopy depth in in.(mm)	11 5/8 (293)
Net weight in lbs. (kg)	31 (14.0)
Length of electrical wire in ft (m)	4 (1.5)
Standard plug fitted	•

DA 2698

Insert ventilation hood

with energy-efficient LED lighting and backlit controls for easy use.




EAN: 4002516023906 / Material number: 10876810 /
Old Material Number: 28269855USA

Minimum distance above electric cooktops in in. (mm)	24 1/8 (610)
Minimum height above gas cooktop (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	26 (660)
Number of phases	1
Total connected load in kW	0.36
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
Installation note	
Vent connection at top	•
Vent connection at top and rear	•
Diameter of vent connection in in.(mm)	6 (150)
Standard accessories	
Communication module for Con@ctivity XKM 2000 DA	XKS 3000 Z
Non-return flap	•

DA 2698

Insert ventilation hood

with energy-efficient LED lighting and backlit controls for easy use.



DA 2698 I- Integrated cooker hood (Installation drawing) – US

1) Vent connection alternatively to rear