

## DA 4248 V D Puristic Varia Island décor hood

with energy-efficient LED lighting and backlit controls for easy use.



- Timeless design – stainless steel canopy 47 1/4 (1198) in (mm) wide
- Unique user convenience – Con@ctivity
- Motorized chimney
- Powerful – ?? in Booster level
- Energy-efficient and quiet

EAN: 4002515990162 / Material number: 10877250 /  
Old Material Number: 28424855USA

<b>Construction type and design</b>	
Color	Stainless steel
<b>Design</b>	
Island ventilation hood	•
<b>Operating modes</b>	
Recirculated mode	Exhaust air
<b>User convenience</b>	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number excl. Intensive)	3
Booster levels	1
Programmable Intensive switch-off	•
Delayed shutdown for 5 or 15 minutes	•
Grease filter saturation indicator	•
Acoustic package	•
Hood in Motion	•
<b>Cleaning convenience</b>	
Easy-to-clean CleanCover hood liner	•
<b>Filter system</b>	
Number of dishwasher-safe stainless-steel grease filters	6
<b>Lighting</b>	
LED	•
Number x W	4 x 3 W
Light intensity in lx	600 lx
Color temperature in K	3500 Kelvin
Light dimmer function	•
<b>Blower</b>	
Dual-action blower	•
AC motor	•
<b>Exhaust air</b>	
Maximum air throughput in cfm according to HVI	430
Air throughput	Values upon request
<b>Safety</b>	
Safety shut-off	•
<b>Technical data</b>	
Overall min. height for vented and external in in. (mm)	29 3/4 (755)
Canopy width in in.(mm)	47 1/4 (1198)
Overall max. height for vented and external in in. (mm)	41 1/4 (1045)
Canopy height in in.(mm)	2 7/8 (70)
Canopy depth in in.(mm)	27 1/2 (698)
Net weight in lbs. (kg)	109 (49.0)
Hard-wired	•
Minimum distance above electric cooktops in in. (mm)	24 1/8 (610)
Minimum height above gas cooktop (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	26 (660)
Number of phases	1
Total connected load in kW	0.51

DA 4248 V D Puristic Varia

Island décor hood

with energy-efficient LED lighting and backlit controls for easy use.



EAN: 4002515990162 / Material number: 10877250 /  
Old Material Number: 28424855USA

Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60

#### Installation note

Vent connection at top	•
Diameter of vent connection in in.(mm)	6 (150)
Telescopic chimney	•


#### Standard accessories

Communication module for Con@ctivity XKM 2000 DA	XKS 3000 Z
Non-return flap	•

## DA 4248 V D Puristic Varia

### Island décor hood

with energy-efficient LED lighting and backlit controls for easy use.



DA 4248 V (Installation drawing) USA

1) Installation area/site, 2) Installation alternatively with spacer frame, 3) A supply lead, and for vented mode flexible vent ducting, must be pre-fitted for the connection in the ceiling to the connection of the cooker hood.