

SC

Steam condenser

For effective moisture removal from and cooling of exhaust air.



- Only suitable for use in combination with a drying unit
- Can be connected to on-site cooling water circuit

EAN: 4002516024323 / Material number: 10928990 / Old Material Number: 69251300D

<b>Product category</b>	
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
PLW 8615	•
PLW 8616	•
PLW 8617	•
<b>Product characteristics</b>	
Material	Stainless steel
<b>Dimensions and weight</b>	
External dimensions, gross height in inches	30 3/8 (770)
External dimensions, gross width in inches	47 1/4 (1200)
External dimensions, gross depth in inches	31 1/2 (800)
Net weight in lbs	31 (14.00)
Gross weight in lbs	298 (135.00)
<b>Standards, test certificates, and symbols</b>	
UL	•