

DP [50Hz]

Drain pump

For converting machines with drain valves to drain pumps.

EAN: 4002516024057 / Material number: 10931330 / Old Material Number: 69240003D



- For installations without a floor drain

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PLW 8615	•
PLW 8616	•
PLW 8617	•
Product characteristics	
Material	Stainless steel, Plastic
Color	Stainless Steel, Black, White, Grey
Application area	
Reprocessing of laboratory glassware	•
Dimensions and weight	
External dimensions, gross height in inches	7 1/8 (180)
External dimensions, gross width in inches	15 3/8 (390)
External dimensions, gross depth in inches	15 3/8 (390)
Net weight in lbs	9 (3.88)
Gross weight in lbs	13 (5.73)