

DA 5428 W Puristic Arca
Wall ventilation hood
with energy-efficient LED lighting and backlit controls for easy use.



- Distinctive design – 47 1/4 (1198) in (mm) wide stainless steel ventilation hood
- Unique user convenience – Con@ctivity
- Energy-efficient and quiet
- Safe and easy to clean – Miele CleanCover

EAN: 4002516057390 / Material number: 10934860 /
Old Material Number: 28542850USA

Construction type and design	
Color	Stainless steel
Design	
Wall ventilation hood	•
Operating modes	
Recirculated mode	Exhaust air
User convenience	
Miele@home	•
Automatic function	Con@ctivity 3.0
Electronic controls	•
Power levels (number excl. Intensive)	3
Operation	Light-touch switches with LEDs
Miele@mobile app	•
Booster levels	1
Programmable Intensive switch-off	•
Delayed shutdown for 5 or 15 minutes	•
Grease filter saturation indicator	•
Acoustic package	•
Cleaning convenience	
Easy-to-clean CleanCover hood liner	•
Filter system	
Number of dishwasher-safe stainless-steel grease filters	4
Lighting	
LED	•
Number x W	4 x 3 W
Light intensity in lx	400 lx
Color temperature in K	3000 Kelvin
Blower	
Dual-action blower	•
AC motor	•
Exhaust air	
Maximum air throughput in cfm according to HVI	418
Air throughput	Values upon request
Safety	
Safety shut-off	•
Technical data	
Overall hood height for vented mode and external in inches (mm)	29 3/8 (745)– 41 5/8 (1055)
Overall hood height for recirculation and external in inches (mm)	34 1/2 (875)– 46 3/4 (1185)
Overall min. height for vented and external in in. (mm)	29 3/8 (745)
Canopy width in in.(mm)	47 1/4 (1198)
Overall max. height for vented and external in in. (mm)	41 5/8 (1055)
Canopy height in in.(mm)	4 3/4 (120)
Overall min. height for recirculation in in. (mm)	34 1/2 (875)
Canopy depth in in.(mm)	20 1/2 (520)
Overall max. height for recirculation in in. (mm)	46 3/4 (1185)

DA 5428 W Puristic Arca

Wall ventilation hood

with energy-efficient LED lighting and backlit controls for easy use.



EAN: 4002516057390 / Material number: 10934860 /
Old Material Number: 28542850USA

Net weight in lbs. (kg)	83 (37.5)
Length of electrical wire in ft (m)	2 (0.8)
Standard plug fitted	•
Minimum distance above electric cooktops in in. (mm)	24 1/8 (610)
Minimum height above gas cooktop (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	26 (660)
Number of phases	1
Total connected load in kW	0.36
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
Installation note	
Vent connection at top	•
Vent connection at top and rear	•
Diameter of vent connection in in.(mm)	6 (150)
Telescopic chimney	•
Standard accessories	
Reducer from 150 to 125 mm Ø	•
Non-return flap	•

