

DA 5428 W Puristic Arca  
Wall ventilation hood  
with energy-efficient LED lighting and backlit controls for easy use.



- Distinctive design – 47 1/4 (1198) in (mm) wide stainless steel ventilation hood
- Unique user convenience – Con@ctivity
- Energy-efficient and quiet
- Safe and easy to clean – Miele CleanCover

EAN: 4002516057390 / Material number: 10934860 /  
Old Material Number: 28542850USA

<b>Construction type and design</b>	
Appliance colour	Stainless steel
<b>Design</b>	
Wall ventilation hood	•
<b>Operating modes</b>	
Recirculated mode	Exhaust air
<b>User convenience</b>	
Miele@home	•
Automatic function	Con@ctivity 3.0
Automatic function Con@ctivity	•
Electronic controls	•
Operation	Light-touch switches with LEDs
Miele@mobile app	•
Power levels (number excl. Intensive)	3
Booster levels	1
Delayed shutdown for 5 or 15 minutes	•
Grease filter saturation indicator	•
Acoustic package	•
<b>Cleaning convenience</b>	
Easy-to-clean canopy interior – CleanCover	•
<b>Filter system</b>	
Number of dishwasher-safe stainless steel grease filters (10-ply)	4
<b>Lighting</b>	
Number x W	4 x 3 W
Light intensity in lx	400 lx
Color temperature in K	3000 Kelvin
<b>Blower</b>	
Dual-action blower	•
AC motor	•
<b>Exhaust air</b>	
Maximum air throughput in cfm according to HVI	418
Air throughput	Values upon request
<b>Safety</b>	
Safety shut-off	•
<b>Technical data</b>	
Overall hood height for vented mode and external in inches (mm)	29 3/8 (745)– 41 5/8 (1055)
Overall height for recirculation mode ventilation hoods in mm	34 1/2 (875)– 46 3/4 (1185)
Canopy width in in.(mm)	47 1/4 (1198)
Overall min. height for vented and external in in. (mm)	29 3/8 (745)
Overall max. height for vented and external in in. (mm)	41 5/8 (1055)
Canopy height in in.(mm)	4 3/4 (120)
Overall min. height for recirculation in in. (mm)	34 1/2 (875)
Canopy depth in in.(mm)	20 1/2 (520)
Overall max. height for recirculation in in. (mm)	46 3/4 (1185)
Net weight in lbs. (kg)	83 (37.5)

## DA 5428 W Puristic Arca

### Wall ventilation hood

with energy-efficient LED lighting and backlit controls for easy use.




EAN: 4002516057390 / Material number: 10934860 /  
Old Material Number: 28542850USA

Length of electrical wire in ft (m)	2 (0.8)
Standard plug fitted	•
Minimum height above electric cooktops in mm	24 1/8 (610)
Minimum safety distance above gas cooktops (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	26 (660)
Number of phases	1
Total connected load in kW	0.36
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
<b>Installation note</b>	
Vent connection at top	•
Vent connection at top and rear	•
Diameter of vent connection in in.(mm)	6 (150)
Telescopic chimney	•
<b>Standard accessories</b>	
Reducer from 150 to 125 mm Ø	•
Non-return flap	•

## DA 5428 W Puristic Arca

### Wall ventilation hood

with energy-efficient LED lighting and backlit controls for easy use.



DA 5428 W(Installation drawing)

1) and 2) Shaded area for vent cut-out